



REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	BP	—	NO	2-8-18
B		607F WAS 3000 PCS PER REEL	LD		CS	6-7-22




LED SCHEMATIC

NOTES:


- DIALIGHT P/N: 597-7715-602F, 597-7715-607F
SUFFIX -602F FOR 20 PCS ON A SAMPLE TAPE STRIP
SUFFIX -607F FOR 7" DIAMETER REEL, PACKAGED 4000 PCS PER REEL.
- LABELING FOR REEL AND OUTSIDE OF ALUMINUM FOIL BAG:
DIALIGHT P/N, QUANTITY PER REEL, DATE CODE, INTENSITY BIN CODE,
LOT NUMBER AND COUNTRY OF ORIGIN.
- TAPE AND REEL LEDS MAY REQUIRE RE-TAPING AFTER TWELVE MONTHS.
- ESD WITHSTAND VOLTAGE 2KV ACC. TO JESD22-A114-D

OPERATING CHARACTERISTICS AT 25° C AMBIENT											
LED COLOR	PEAK WAVELENGTH (nm)	LUMINOUS INTENSITY (mcd) @ I _F =5mA			DOMINANT WAVELENGTH (nm) @ I _F =5mA			FORWARD VOLTAGE (V) @ I _F =5mA			VIEWING ANGLE (DEGREES)
	TYP	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	TYP
RED	632	15	—	50	617	—	629	1.60	—	2.30	130
GREEN	518	71	—	145	525	—	540	2.50	—	3.30	
BLUE	468	10	—	30	465	—	475	2.50	—	3.10	


ABSOLUTE MAXIMUM RATINGS AT 25° C AMBIENT					RED	GREEN	BLUE	UNITS
POWER DISSIPATION					50	38		mW
CONTINUOUS FORWARD CURRENT					20	10		mA
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 10ms PULSE WIDTH)					40			mA
ELECTROSTATIC DISCHARGE THRESHOLD (HBM)					2000			V
REFLOW SOLDERING TEMPERATURE FOR 10 SEC.					260			°C
OPERATING TEMPERATURE					-20 TO +80			°C
STORAGE TEMPERATURE					-30 TO +85			°C



PACKAGE DIMENSION OF TAPE AND REEL



RECOMMENDED ROHS SOLDER PROFILE



ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.		
DIALIGHT CORP INTERNAL REFERENCE ONLY = 3D MODEL : 4500521846016-A.3		
SCALE: 20.000	DRAWING NUMBER	REV
ALL DIM's: INCH (mm)	C-18374	B
TOLERANCES: UNLESS OTHERWISE SPECIFIED	TITLE	
FRACTIONS: ±1/64	SM 0606 R,G,B W ZENER LC 5mA	
DECIMALS (.XX): ±.01	MATERIAL	
DECIMALS (.XXX): ±.005		
DECIMALS (.XXX): ±.0005		
ANGLES: ±1°		
FINISH		
FSCM 83330		
SHEET 1 OF 1	FAMILY TABLE:	

Dialight
1501 ROUTE 34 SOUTH
FARMINGDALE, NJ 07727
(732) 919-3119
www.dialight.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

5977715607F