



Certifications & Ratings

- RoHS compliant

Application


The 680 Series LED Panel Mount Indicators are designed for a variety of applications such as:

- Main power indication
- Remote power indication
- Status indication
- Maintenance and warning indication
- Instrumentation
- ... and many more!


Dimensions

inches [mm]


Standard



Snap-in



6" Wire Leads



Mechanical Information

Mounting Hole Size: 0.413" (10.5 mm) (Standard)
Snap-in, see drawing

Max Panel Thickness: 0.236" (6.0 mm) (Standard);
0.098" (2.49 mm) (Snap-in)

Mounting Torque: 0.217 lbs/ft (3 kg/cm) (Standard)

Specifications

Voltage Options: 6, 12, & 24 VDC (no resistor required)

Operating Temp: -20 °C to +75 °C (-4 °F to +167 °F)

Storage Temp: -40 °C to +100 °C (-40 °F to +212 °F)

Electrical Connection: Solder terminals, 6" wire leads

Housing: Polycarbonate


Terminals: Copper—Nickel Plated

Lock Washer: Iron—Nickel Plated

Nut: Brass—Nickel Plated



Ordering Information 680 Series



Dialight P/N			Color	Current (mA)	Typical Intensity (mcd)	Panel Thickness	Termination
6 VDC	12 VDC	24 VDC					

Standard

680-3132-121F	680-3132-131F	680-3132-141F	● Red	15	1530	0.236" (6.0mm)	Solder Terminals
680-3232-122F	680-3232-132F	680-3232-142F	● Green		4330		
680-3332-123F	680-3332-133F	680-3332-143F	● Orange		1455		
680-3432-124F	680-3432-134F	680-3432-144F	● Blue		245		
680-3135-121F	680-3135-131F	680-3135-141F	● Red		1530	0.236" (6.0mm)	Wire Leads
680-3235-122F	680-3235-132F	680-3235-142F	● Green		4330		
680-3335-123F	680-3335-133F	680-3335-143F	● Orange		1455		
680-3435-124F	680-3435-134F	680-3435-144F	● Blue		245		

Snap-in

680-3132-221F	680-3132-231F	680-3132-241F	● Red	15	335	0.098" (2.5mm)	Solder Terminals
680-3232-222F	680-3232-232F	680-3232-242F	● Green		4070		
680-3332-223F	680-3332-233F	680-3332-243F	● Orange		1025		
680-3432-224F	680-3432-234F	680-3432-244F	● Blue		730		
680-3135-221F	680-3135-231F	680-3135-241F	● Red		335	0.098" (2.5mm)	Wire Leads
680-3235-222F	680-3235-232F	680-3235-242F	● Green		4070		
680-3335-223F	680-3335-233F	680-3335-243F	● Orange		1025		
680-3435-224F	680-3435-234F	680-3435-244F	● Blue		730		

Dialight reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.dialightsignalsandcomponents.com

Warranty Statement: Except for the warranty expressly provided for [herein/above/below], Dialight disclaims any and all other warranties, express or implied, including, without limitation, any warranties of merchantability, fitness for a particular purpose, title, and noninfringement.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

680-3335-133F	680-3135-121F	680-3335-243F	680-3235-132F	680-3332-233F	680-3432-234F	680-3135-141F
680-3432-144F	680-3232-222F	680-3132-131F	680-3332-123F	680-3432-134F	680-3435-144F	680-3332-133F
680-3432-124F	680-3132-241F	680-3132-141F	680-3132-231F	680-3435-234F	680-3432-244F	680-3435-244F
680-3235-142F	680-3135-231F	680-3132-221F	680-3432-224F	680-3435-134F	680-3335-223F	680-3332-223F
680-3135-221F	680-3235-232F	680-3335-143F	680-3435-124F	680-3235-242F	680-3232-132F	680-3335-123F
680-3232-142F	680-3235-122F	680-3132-121F	680-3335-233F	680-3232-122F	680-3332-143F	680-3232-232F
680-3135-241F	680-3235-222F	680-3332-243F	680-3435-224F	680-3232-242F	680-3135-131F	679-2425-334F
679-2222-332F	679-2422-324F	679-2325-333F	679-2425-344F	679-2125-331F	679-2312-333F	679-2125-341F
679-2222-342F	679-2212-322F	679-2215-322F	679-2412-334F	679-2225-322F	679-2225-332F	679-2212-332F
679-2312-343F	679-2322-333F	679-2222-322F	679-2425-324F	679-2115-321F	679-2122-321F	679-2122-331F
679-2412-324F	679-2415-344F	679-2322-343F	679-2325-323F	679-2115-341F	679-2225-342F	679-2322-323F
679-2125-321F	679-2315-333F	679-2422-344F	679-2315-323F	679-2315-343F	679-2415-324F	679-2122-341F
679-2212-342F	679-2115-331F	679-2215-332F	679-2325-343F	679-2312-323F	679-2415-334F	679-2422-334F
679-2215-342F	679-2112-341F	679-2412-344F				