

[Request more info](#)
Part Number : 5219901F




This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	521
Configuration	3 mm Lens
Description	3 mm Discrete White WC
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Single Color
Lens Color	Water Clear

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	30mA
Reverse Current	10μA @ Vr = 5V
Forward Current Pulsed	100mA
Derating	from 37° @ .42mA/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-40~+85
Storage Temperature	-40~+100

Operating Characteristics

LED Type	InGaN
Color	White
Luminous Intensity Min	950
Luminous Intensity Max	2900
Test Current mA	20mA
Power Dissipation Max	110mW

[EAX Login](#) 
[Site Map](#)
[Privacy and Cookies Policy](#)
[Terms and Conditions](#)
[Dialight BTI](#)
[Alert Services](#)


Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

521-9901F