




USB-TO-SERIAL  
CONVERTERS



# EDGEPORT

Easy out-of-the-box solution for I/O expansion is available in a wide variety of configurations for maximum flexibility and scalability

Digi Edgeport® USB-to-serial converters offer instant I/O expansion for peripheral device connectivity.

An out-of-the-box (external) alternative to PCI cards, Edgeport makes it easy to add serial and USB ports to a PC, server or thin client in minutes – without opening the chassis, reconfiguring or rebooting the system.

Edgeport is available in multiple configurations for maximum flexibility and scalability.

Choose from compact form factors for space-prohibitive applications; single port “bump-in-the-cable” solutions for notebook expansion; software-selectable RS-232/422/485 models to connect any type of serial device to one box; and DB-9 or DB-25 connectors to meet cabling requirements.

Feature-rich design, reliability and unmatched operating system support make Edgeport USB-to-serial converters ideal for mission-critical enterprise applications.

## BENEFITS

- Add 1, 4, 8 or 16 serial ports to a PC, thin client or server in minutes
- Designed for peripheral device connectivity in retail stations, self check-out systems, emergency vehicles, kiosks, ATMs and more
- Software selectable MEI and industrial models
- Low total cost of ownership with external, user-installable solution

## RELATED PRODUCTS



AnywhereUSB® Plus




Hubport®



Connectport® TS 16




PortServer® TS 4



Cables and Accessories

## APPLICATION EXAMPLE

### POS CONNECTIVITY



## SPECIFICATIONS

Digi Edgeport® Serial

| Digi Edgeport® Industrial

### INTERFACES (VARIES BY MODEL)

<b>SERIAL PORTS</b>	1, 4, 8 or 16	1, 4 or 8
<b>SERIAL TYPE</b>	RS-232	RS-422/485, software selectable RS-232/422/485
<b>SERIAL CONNECTOR</b>	DB-9, DB-25	DB-9
<b>SERIAL DATA RATE</b>	230 Kbps per port simultaneously	230 Kbps per port simultaneously
<b>DOWNSTREAM USB PORTS</b>	2 (16-port models only)	0

### FEATURES

<b>USB</b>	USB 1.0 and USB 1.1 compatible; backwards compatibility for USB 2.0 and USB 3.0; USB-IF certified; Plug and Play	
<b>LEDS</b>	LED displays device status and COM port activity	
<b>OPERATING SYSTEMS</b>	Windows Server® 2019, Windows Server® 2016, Windows 10®, Windows 8®, Windows 7®, Windows Vista®, Windows Server 2012, Windows Server 2008 R2, Windows XP®, Windows XP Embedded, Windows CE® 5, Windows CE 6 (x86 only), Windows Server 2003 R2, Windows 2000®; Linux	
<b>CABLES</b>	1-meter USB cable	1-meter USB cable
<b>OTHER (GENERAL)</b>	Automatic port reacquisition; COM port assignments maintained across reboots; Full hardware and software flow control; No additional IRQ or memory address requirements; Low power consumption; Rack mountable; Hot-swappable	
<b>OTHER (MODEL-SPECIFIC)</b>	N/A	N/A

### POWER REQUIREMENTS

<b>POWER SUPPLY</b>	External power supply not required for models without USB ports (USB powered); Models with USB ports (Edgeport/216) ship with power supply: 100/240 VAC 60/50 Hz at 5 VDC @ 3 Amps max	
---------------------	---	--

### ENVIRONMENTAL

<b>OPERATING TEMPERATURE</b>	0° C to 55° C (32° F to 131° F)	0° C to 55° C (32° F to 131° F)
<b>RELATIVE HUMIDITY</b>	0% to 95% (non-condensing)	0% to 95% (non-condensing)

### REGULATORY APPROVALS

<b>SAFETY</b>	EN60950, UL 1950, CSA 2.2 No. 950, IEC 950	
<b>EMISSIONS/IMMUNITY</b>	CE, FCC Part 15 Class B, EN55022, EN55024	

## SPECIFICATIONS

## Digi Edgeport® Measurements



### EDGEPORT/1, 1i

Length: 8.00 cm (3.15 in)  
 Width: 4.40 cm (1.75 in)  
 Height: 2.03 cm (0.80 in)  
 Weight: 45.36 g (1.60 oz)



### EDGEPORT/4, 4S, 4 DB-25

Length: 11.05 cm (4.35 in)  
 Width: 18.29 cm (7.20 in)  
 Height: 2.61 cm (1.03 in)  
 Weight: 311.00 g (10.00 oz)



### EDGEPORT/8, 8S


Length: 11.05 cm (4.35 in)  
 Width: 18.29 cm (7.20 in)  
 Height: 4.45 cm (1.75 in)  
 Weight: 453.59 g (16.00 oz)



### EDGEPORT/216, EDGEPORT/8 DB-25

Length: 12.70 cm (5.00 in)  
 Width: 43.118 cm (17.00 in)\*  
 Height: 4.53 cm (1.80 in)  
 Weight: 1170.84 g (41.30 oz)

\* 48.26 cm (19.0 in) with optional rack mount ears



PART NUMBERS	DESCRIPTION
301-1004-04	Edgeport/1 - 1 RS-232 serial DB-9
301-1001-15	Edgeport/1i - 1 RS-422/485 serial DB-9
EP-USB-4	Edgeport/4 - 4 RS-232 serial DB-9
EP-USB-4S	Edgeport/4s - 4 RS-232/422/485 serial DB-9; software selectable
EP-USB-4-D25	Edgeport/4 - 4 RS-232 serial DB-25
EP-USB-8	Edgeport/8 - 8 RS-232 serial DB-9
EP-USB-8S	Edgeport/8s - 8 RS-232/422/485 serial DB-9; software selectable
EP-USB-8-D25	Edgeport/8 - 8 RS-232 serial DB-25
EP-USB-216	Edgeport/216 - 2 USB; 16 RS-232 serial DB-9

FOR MORE INFORMATION  
PLEASE VISIT **DIGI.COM**



**DIGI SERVICE AND SUPPORT** / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit [www.digi.com/support](http://www.digi.com/support).

© 1996-2020 Digi International Inc. All rights reserved.  
All trademarks are the property of their respective owners.

91001226  
F7/420

**DIGI INTERNATIONAL WORLDWIDE HQ**  
877-912-3444 / 952-912-3444 / [www.digi.com](http://www.digi.com)

**DIGI INTERNATIONAL GERMANY**  
+49-89-540-428-0

**DIGI INTERNATIONAL JAPAN**  
+81-3-5428-0261 / [www.digi-intl.co.jp](http://www.digi-intl.co.jp)

**DIGI INTERNATIONAL SINGAPORE**  
+65-6213-5380

**DIGI INTERNATIONAL CHINA**  
+86-21-50492199 / [www.digi.com.cn](http://www.digi.com.cn)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

DIGI:

[301-1002-14](#) [301-1000-03](#) [301-1000-81](#) [301-1000-92](#) [301-1001-21](#) [301-1003-30](#) [301-1016-08](#) [301-2016-16](#)