

WITTRA™ MESH ROUTER



Features:

- Small, Rugged Wireless Mesh Router
- Sealed to IP51
- Pre-certified, Ready for Field Deployment
- Secure fixed nodes
- Easy to Set Up, Easy to Use




Description:

The backbone component for message routing in IOT OUT OF THE BOX™, the mesh-router provides scalability by forming a multi-hop network to achieve a larger coverage area for the Sensor Tags.

Specification	
Size	40 x 40 x 15mm (without flex tail) 90 x 40 x 15mm (with flex tail)
Weight	35g
Ambient Operating Temperature	-30°C to +85°C
Environmental Rating	IP51
Battery	360mAH LiPo Rechargeable
Physical Interface	Micro-B USB
Maximum Input Power	100mA @5V (during battery charge)
Average Current Consumption	8mA
Radio Transmit Frequency	863.0—870.0 MHz
Radio Transmit Power	20mW EIRP max
Data Transmission Rate	50kbps (as per IEEE 802.15.4g)
Regulatory Compliance	CE (ETSI EN300 220-1)
Security	DTLS

Mesh Router 1.0



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wittra:

1000285 1000364