



DVC-Rx

The DVC-Rx converts HD/SD-SDI (HD, SD) signals to HDMI for driving HDMI monitors. The DVC-Rx provides loop through outputs for “daisy chaining” multiple monitors or other equipment to the same HD-SDI source.

Fully compliant with the SMPTE 259M-C, SMPTE 292M, SMPTE 296 standards. The LED's indicate input port status and the slide switch provides selection between the two inputs.

VIDEO INPUTS

2 x HD-SDI (75 ohm BNC)

VIDEO OUTPUT

2 x HD-SDI (75 ohm BNC) - loop through
1 x HDMI V1.2 (standard type A connector)

SUPPORTED MODES

HD-SDI

SD Video Format

480i60 (NTSC)
576i50 (PAL)
480p60
576p50

HD Video Format

720p50
720p60
1080i50
1080i60
1080p25
1080p30

Note : Embedded audio not supported.

INPUT PORT SELECTION

HD/SD-SDI input port selection Slide switch

MECHANICAL

Size (H-W-D) 33mm x 108mm x 83mm
Weight 0.5 kg

MOUNTING

Wall Mount Plate 1 pair (Optional)


ENVIRONMENTAL

Operating temperature 0°C to 60°C
Operating humidity 10% to 95%
Storage temperature -20° to 85°
Storage humidity 10% to 95%


POWER

12VDC, 5W (max)


MECHANICAL



PORT DESCRIPTION



MOUNTING (OPTIONAL)



Remark : The four mounting holes are located under the rubber pad.

LED STATUS

ALWAYS ON LED :
Active port selected with valid signal detected.

BLINKING LED :
Active port selected with no signal or invalid signal detected.

ACCESSORIES

420000900-3 : HDMI cable, 2 meter
500003900-3 : POWER SUPPLY - 12V 4.16A

USA

Digital View Inc.

18440 Technology Drive
Morgan Hill, CA 95037,
USA

Tel : +1 (408) 782-7773

EUROPE

Digital View Limited

6 Marylebone Passage
London, W1W 8EX
UK

Tel : +44 (0) 20-7631-2150

ASIA

Digital View Ltd.

16th Floor Millennium City 3
370 Kwun Tong Road
Kwun Tong, Hong Kong

Tel : (852) 2861-3615

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Digital View:](#)

[420000900-3](#)