

ELECTRONIC HID BALLASTS

Case Material: Metal

Input	
Nominal Voltage	Universal 120V to 277V
Frequency	50/60Hz
Line Regulation	± 5% output variation over full input range
Power Factor	> 0.95
Total Harmonic Distortion	< 10%

Output	
Lamp Operating Frequency	165Hz Square Wave
Lamp Current C.F.	<1.3

Ordering Information	
Standard Case Quantity	50 Units
Unit Weight/Case Weight	0.51 lbs/28 lbs

ELECTRICAL SPECIFICATIONS

Watts	Hatch Part Number	Description	Lamp Types/ANSI Codes	Voltage Range	Nominal Input Power	Input Current/ Input Voltage	Max. Remote Distance (ft)
39	MC39-1-F-UNNU	39 Watt Universal Mini w/Feet	M130 Ceramic MH	Wide Range Input 108-305VAC	44 Watts	.37 Amps @ 120V	25
	MC39-1-J-UNNU	39 Watt Universal Mini Bottom Feed w/Studs				.22 Amps @ 208V .19 Amps @ 240V .16 Amps @ 277V	

PRODUCT FEATURES :

- Thermal protection
- Approved for recessed use
- Micro Processor Controlled
 - Safety Shut Down Features
 - Superior Hot Lamp Restrike Characteristic
- Low Voltage Lamp Shutdown
- Sound Rated: A
- Minimum Starting Temperature: -30°C
- Maximum Case Temperature: 80°C
- Complies with FCC Part 18 (Class B) Consumer limits
- Up to 5 Year Warranty
- Lamp end-of-life protected

- Transient Protection Meets ANSI/IEEE C62.41 Cat A
- Short Circuit Protection
- Open Circuit/No Lamp/ Hot Lamp Shutdown, Retry and Ignition Failure Protection:

Ignition failure shutdown in 5 seconds followed by multiple timed restrikes with lamp ignition or timed shutdown until power is reset (restrike timing is lamp wattage dependent)


APPROVALS:




Type 1 Outdoor




WIRING DIAGRAMS:




MOUNTING DIAGRAM:



CASE DIMENSIONS & MECHANICAL SPECIFICATIONS:



Center line to center line is .16" less than end to end on models with mounting feet.



CASE STYLE

MOUNTING

U - Mini

F - With feet

Wiring Information

Lead Length : Input/Output : 8"
Wire Type : Input: 18AWG, 105°C, 600V

Operating Temperatures

Minimum Starting Temperature : -30°C
Maximum Case Temperature : 80°C

CASE STYLE

MOUNTING

U - Mini

J - Bottom feed with studs


Wiring Information

Lead Length : Input/Output : 10"
Wire Type : Input: 18AWG, 105°C, 600V

Operating Temperatures

Minimum Starting Temperature : -30°C
Maximum Case Temperature : 80°C

CASE STYLE SIZE CHART:



Each case style listed in the Size Chart represents a side lead model with no mounting feet. All HATCH E-HID Ballasts are available in several mounting and wiring configurations, each with slightly different dimensions from those listed in the chart.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hatch Lighting:](#)

[MC39-1F-UNNU](#) [MC39-1J-UNNU](#)