

ELECTRONIC LOW VOLTAGE TRANSFORMER

Input Voltage	120VAC, 277VAC - 50-60Hz
Output	11.5 VAC
Enclosure Material	Aluminum
Weight	6.4 oz.
Power Factor	> 0.95
Operating Frequency	25KHz
Total Harmonic Distortion	≤ 20%
Input	6", 18AWG stranded, 105°C stripped 3/8" tinned
Output	6", 18AWG stranded, 105°C stripped 3/8" tinned

ENVIRONMENTAL SPECIFICATIONS

Maximum Case Temperature	90°C
Minimum Starting Temperature	-30°C
Sound Rating	A+
Operating Humidity	95% relative humidity, non-condensating
Environmental Protection	Epoxy Sealed for moisture resistance and shock/vibration resistance

PRODUCT FEATURES:

- High Reliability
- Moisture Resistant
- Emits no audible noise
- Low Harmonic Distortion
- High power factor
- Lightweight, compact design
- Small case size
- Works with most commercially available dimmers. Hardwire electronic dimmers are recommended for optimum performance.

APPROVALS:

- Class P Type 1
Outdoors



ELECTRICAL FEATURES

Soft Start Circuitry

All models of Hatch low-voltage transformers utilize a soft start circuitry to maximize lamp life. The soft start circuit ramps up the lamp filament voltage slowly when the lamp is cold.

NOTE: Instant Start on Hot Lamp Re-Strike

Electronic Short Circuit Program


All Hatch low-voltage transformers employ our (ESP) Electronic Short Circuit and overload protection. The ESP sensing circuit will instantly shut down the output before any of the components are stressed if a short circuit or over load is detected. The transformer will automatically reset as soon as the fault is corrected.

HARDWIRE ELECTRONIC


Max Watts	Min Watts	Hatch Part Number	Input Volts	Output Volts	Input Amps	Output Amps	Case Style	Safety Listing
150	10	RS12-150	120	11.5	1.25	13.05	A	UL/C-UL Recognized
		RS12-150BF					B	
		RS24-150		23.5		6.39	A	
		RS12-150-277*	277	11.5	0.55	13.05	A	
		RS12-150-277BF*					B	

* NOTE: Must use a minimum of 20 watts when using dimmers. It is also important to confirm dimming controls compatibility with the manufacturer and your Hatch representative. 277 Volt dimming not recommended.

DIMENSIONS:



WIRING DIAGRAM:



NOTES:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hatch Lighting:](#)

[RS12-150](#) [RS12-150-277](#) [RS12-150BF](#) [RS24-150WD](#)