


PART REVISION HISTORY			
REV.	DESCRIPTION	DATE	APPROVED
1	Part Creation	10/16/17	Shane N.



General Notes:

-This document supersedes any accompanying CAD models. Any goods sold must comply with this document.

-Max radius of internal fillets = 0.10mm

-All edges are edge break unless specified.

-RoHS Compliant

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS ALTERNATE UNITS FOR REFERENCE ONLY Tolerances Are: X.X ± 0.2 mm (0.008") X.XX ± 0.10 mm (0.004") X.XXX ± 0.050 mm (0.0020") Angular: ± 0.5 Degree	APPROVALS		DATE			DIODE LASER CONCEPTS, INC.		
	Drawn By: Shane N.		10/16/2017			2027 Commerce Dr Medford, Oregon 97504 USA		
	Checked By: Shane N.		10/16/2017		Description: Laser Mount; 0.75" OD Modules; RoHS Compliant			
	Approved By: Mike R.		10/16/2017		Part Number: 0058-0007		Part Rev: 1	
FINISH 0.8 	Material: Hard Anodized Aluminum				SIZE A	Scale: 1:1		SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Diode Laser Concepts:](#)

[0058-0007](#)