




Scale 2:1



Note:

1. LEAD WIRE UL 1061 #26AWG
Pin1. <BLACK> GND(-)
Pin2. <YELLOW> VCC(+)
Pin3. <GREEN> Signal(FG)
Pin4. <BLUE> PWM INPUT
2. HOUSING: 2543-4P or EQUIVALENT



REV	DESCRIPTION	Section	Date
1	首次發行		2019.08.26
2	加註 pipe & fin detailed dimension	加註於 page.6	2020.09.15

14	RGE-ST002-1	LABLE	1
13	GREASE	GREASE X23-7762 30*30*0.15mm	1
12	AL FIN (30 FINS)	AL 1050 沖壓	1
11	HEAT PIPE	C1020 Ø6 燒結管 折彎 抗氧化	3
10	AL BASE	AL 壓鑄成型	1
9	CLIP SCREW	SAE C1018 或 SAE 1215MS 鍍色 M3*5.1X39.5mm	4
8	CLIP Spring	SPRING_SWP 鍍色 Ø1.3x25.9Lmm 8圈	4
7	COVER SEREW	SAE C1018 或 SAE 1215MS 鍍色 M2*5mm	4
6	I156 CLIP	I156_CLIP	1
5	E-RING	SK7 鍍色 Ø9.0x0.6mm	4
4	AL BASE SCREW	SAE C1018 或 SAE 1215MS 鍍色 M3*8mm	4
3	FAN SCREW	SAE C1018 或 SAE 1215MS 鍍色 M3*29.9mm	4
2	FAN 6025	FAN 6025, EVERFLOW P/N: R126025BUAF7C8cR	1
1	FAN COVER	AL 5052 T=1.0mm 沖壓折彎	1
ITEM	PART	DESCRIPTION	QTY

PROPRIETARY NOTE:

This document contains confidential information and proprietary to Rego Electronics and shall not be reproduced or disclosed to other documents or used for any purpose other than that for which was obtained without the expressed written consent of Rego Electronics.

.X ± 0.30	APPROVED: Chris	 http://www.rego.com.tw
.XX ± 0.20	CHECKED: Levi	
.XXX ± 0.15	DRAWN: Vic	
X* ± 3'		
UNITS: mm	SCALE: NONE	TITLE: 2U CPU Cooler For Intel I15x Processors
		PART NO: RG3216-EF-A004
		SHEET: 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rego Electronics:](#)

[RG3216-AD-A004](#)