



## Alpha 41

GSM/UMTS/LTE/WiFi and Bluetooth Antenna

### Key Features

- Overall Frequency Coverage 700-960 and 1700-2700MHz
- Ideal for Wireless LAN and Bluetooth
- Slim unobtrusive design



### General Description

The Alpha 41 is a flexible over moulded antenna designed for vertical polarisation but having similar properties in the horizontal plane. The antenna comes fitted with a quality 3M adhesive pad for simple installation.

The wide bandwidth of the antenna makes it ideal for multiple uses across both telephony and WiFi.

### Additional Considerations

- Does not rely on mounting on metallic surface
- WiFi, Bluetooth and ZigBee compatible
- Meets all EU compliance criteria for electronic goods

A Adhesive	2G GSM	3G UMTS	4G LTE
WLAN 2400	ISM 2450	BLE Bluetooth	ZB Zigbee

## Alpha 41


GSM/UMTS/LTE/WiFi and Bluetooth Antenna

### Electrical Specifications

Impedance:	50 Ohm
Gain:	700 - 960MHz 0dBi 1700 - 2700MHz 2dBi
VSWR:	$\leq 3.6 : 1$
Frequency:	700 - 960 / 1700 - 2700MHz
Max Power:	50W
Polarization:	Vertical

### Mechanical Specifications

Dimensions:	132 x 22.5 x 7mm
Cable:	RG174
Connector:	SMA Plug
Mounting Method:	Double sided tape







## Alpha 41

GSM/UMTS/LTE/WiFi and Bluetooth Antenna

### Return Loss



### VSWR



### Ordering Details

Part Number	Description
ALPHA41/2M/SMAM/RP/S/19	GSM/UMTS/LTE/WiFi and Bluetooth Antenna, 2m Cable SMA Male Reverse Polarity
ALPHA41/3M/SMAM/S/S/19	GSM/UMTS/LTE/WiFi and Bluetooth Antenna, 3m Cable SMA Male

Registered in England No. 08405712  
VAT Registration No. GB163 04 0349

Siretta Ltd  
Basingstoke Road  
Spencers Wood  
Reading  
Berkshire RG7 1PW

sales  
fax  
email  
web

+44(0)118 976 9014  
+44(0)118 976 9020  
sales@siretta.com  
www.siretta.com

Rev 1.3

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siretta:

[ALPHA41/2M/SMAM/RP/S/19](#) [ALPHA41/3M/SMAM/S/S/19](#)