

The ECS-3225SMV is a miniature SMD HCMOS Oscillator with MultiVolt™ capability of 1.62 ~ 3.63 V with a tight stability of ± 5 or ± 10 ppm. The 3.2 x 2.5 x 1.2 mm ceramic package is ideal for Low Power/Portable, Industrial, and IoT applications.

[Request a Sample](#)

OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS



- 3.2 x 2.5 mm Footprint
- Extended Temp Range
- RoHS Compliant
- Wide Supply Voltage
- Low Jitter
- Compatible with 1.8V, 2.5V or 3.3V Power Supply

DIMENSIONS (mm)




Figure 1) Top, Side, and Bottom views

PARAMETERS	CONDITIONS	ECS-3225SMV			UNITS
		MIN	TYP	MAX	
Frequency Range		8.000		60.000	MHz
* Frequency Stability	-40 ~ +105°C (FP Opt)			± 10	ppm
Supply Voltage		1.62		3.63	V
Output Load	CMOS			15	pF
Output voltage Level	VOL: 0.2 Vdd max. / VOH: 0.8 Vdd min. V DC				
Rise & Fall time	20% Vdd – 80% Vdd			5	nS
Start Up Time				10	mS
Phase Jitter	12 kHz to 20 MHz			1	pS
Duty Cycle	@ 1/2 Vdd		45/55		%
Input Current (No Load)			6	10	mA
Standby Current				10	μ A
Operating Temp*	P Option	-40		+105	°C
Storage Temp		-55		+125	°C

PAD CONNECTIONS

1	Tri-state
2	Gnd
3	Output
4	Vdd

Tri State Function

Pin 1	Output
0.7 * Vdd Min or NC	Active
0.3 * Vdd Max.	High Impedance




Figure 2) Suggested Land Pattern

PART NUMBERING GUIDE: Example ECS-3225SMV-250-FP-TR

ECS	SERIES	FREQUENCY ABBREVIATION	* STABILITY	TEMP RANGE -	PACKAGING
ECS	3225SMV 3.2 x 2.5 mm MultiVolt™ Oscillator Tight Stability	250 = 25.000 MHz See Developed Frequencies Pg. 2	F = ± 10 ppm G = ± 5 ppm	N = -40 ~ +85°C P = -40 ~ +105°C	-TR = Tape & Reel 1K/Reel


* Frequency Stability includes initial tolerance, temperature, supply voltage and load change reflow frequency shift, and aging.

Rev. 2019


DEVELOPED FREQUENCIES

FREQUENCY MHz	CODE
8.000	80
10.000	100
11.0592	110.5
12.000	120
16.000	160
19.200	192
20.000	200
24.000	240
25.000	250
26.000	260
27.000	270
32.000	320
33.000	330
33.333	333.3
48.000	480
50.000	500

SOLDER PROFILE
Peak solder Temp +260°C ±5°C 10 ±5 Sec Max.
2 Cycles Max.
MSL 1, Lead Finish Au



POCKET TAPE DIMENSIONS (mm)



A	B	C	D	F	J	L	M	Reel Dia.	Qty/Reel
3.4	2.7	8.0	3.5	4.0	1.0	0.25	1.4	178	1000pcs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ECS:

[ECS-3225SMV-080-FN-TR](#) [ECS-3225SMV-080-FP-TR](#) [ECS-3225SMV-080-GP-TR](#) [ECS-3225SMV-100-FN-TR](#)
[ECS-3225SMV-100-FP-TR](#) [ECS-3225SMV-500-GP-TR](#) [ECS-3225SMV-330-GP-TR](#) [ECS-3225SMV-480-FN-TR](#) [ECS-](#)
[3225SMV-480-FP-TR](#) [ECS-3225SMV-480-GP-TR](#) [ECS-3225SMV-500-FN-TR](#) [ECS-3225SMV-500-FP-TR](#) [ECS-](#)
[3225SMV-270-GP-TR](#) [ECS-3225SMV-320-FN-TR](#) [ECS-3225SMV-320-FP-TR](#) [ECS-3225SMV-320-GP-TR](#) [ECS-](#)
[3225SMV-330-FN-TR](#) [ECS-3225SMV-330-FP-TR](#) [ECS-3225SMV-250-GP-TR](#) [ECS-3225SMV-260-FN-TR](#) [ECS-](#)
[3225SMV-260-FP-TR](#) [ECS-3225SMV-260-GP-TR](#) [ECS-3225SMV-270-FN-TR](#) [ECS-3225SMV-270-FP-TR](#) [ECS-](#)
[3225SMV-200-GP-TR](#) [ECS-3225SMV-240-FN-TR](#) [ECS-3225SMV-240-FP-TR](#) [ECS-3225SMV-240-GP-TR](#) [ECS-](#)
[3225SMV-250-FN-TR](#) [ECS-3225SMV-250-FP-TR](#) [ECS-3225SMV-160-GP-TR](#) [ECS-3225SMV-192-FN-TR](#) [ECS-](#)
[3225SMV-192-FP-TR](#) [ECS-3225SMV-192-GP-TR](#) [ECS-3225SMV-200-FN-TR](#) [ECS-3225SMV-200-FP-TR](#) [ECS-](#)
[3225SMV-100-GP-TR](#) [ECS-3225SMV-120-FN-TR](#) [ECS-3225SMV-120-FP-TR](#) [ECS-3225SMV-120-GP-TR](#) [ECS-](#)
[3225SMV-160-FN-TR](#) [ECS-3225SMV-160-FP-TR](#) [ECS-3225SMV-110.5-GP-TR](#) [ECS-3225SMV-333.3-FN-TR](#) [ECS-](#)
[3225SMV-333.3-GP-TR](#) [ECS-3225SMV-110.5-FP-TR](#) [ECS-3225SMV-333.3-FP-TR](#) [ECS-3225SMV-110.5-FN-TR](#)