





TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.3
.XX	±0.2
.XXX	±0.1

THIS IS A C.A.D. GENERATED DRAWING  
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①



RECOMMENDED PCB LAYOUT

#### SPECIFICATIONS

VOLTAGE RATING: 250V AC/DC  
CURRENT RATING: 3A AC/DC  
WITHSTANDING VOLTAGE: 1000V AC/MIN  
TEMPERATURE RANGE: -40°C TO 105°C  
INSULATION RESISTANCE: ≥ 1000 MΩ  
CONTACT RESISTANCE: ≤ 10mΩ

INSULATOR MATERIAL: LCP, UL94V-0  
COLOR - NATURAL

CONTACT: BRASS, TIN PLATED

MATES WITH HOUSING: 14K-502-210-AA2

PACKAGING: TAPE AND REEL



THIS SERIES FULLY CONFORMS TO  
THE EUROPEAN UNION DIRECTIVES  
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC  
TORONTO, ONTARIO  
CANADA

THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF EDAC INC., AND  
SHALL NOT BE REPRODUCED, OR COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OR SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.

14K SERIES SMT, 2.50 PITCH, SIDE ENTRY	ACAD REFERENCE NO.: 14K Assembly		UNIT: MM
	DRAWN: V.K.	DATE: 02/16/24	
	CHECKED: R.S.M.	DATE: 02/21/24	
	SCALE: 2.5:1	SHEET 1 OF 1	
	DRAWING NUMBER: 14K-502-418TAA1	ISSUE 1	
	PART NUMBER: 14K-502-418TAA1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EDAC:](#)

[14K-502-418TAA1](#)