





TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.3
.XX	±0.2
.XXX	±0.1

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①



RECOMMENDED PCB LAYOUT

SPECIFICATIONS

VOLTAGE RATING: 250V AC/DC
CURRENT RATING: 3A AC/DC
WITHSTANDING VOLTAGE: 1000V AC/MIN
TEMPERATURE RANGE: -40°C TO 105°C
INSULATION RESISTANCE: ≥ 1000 MΩ
CONTACT RESISTANCE: ≤ 10mΩ

INSULATOR MATERIAL: LCP, UL94V-0
COLOR - NATURAL

CONTACT: BRASS, TIN PLATED

MATES WITH HOUSING: 14K-504-210-AA2

PACKAGING: TAPE AND REEL



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

14K SERIES SMT, 2.50 PITCH, SIDE ENTRY	ACAD REFERENCE NO.: 14K Assembly		UNIT: MM
	DRAWN: V.K.	DATE: 02/16/24	
	CHECKED: R.S.M.	DATE: 02/21/24	
	SCALE: 2.5:1	SHEET 1 OF 1	
	DRAWING NUMBER: 14K-504-418TAA1	ISSUE 1	
	PART NUMBER: 14K-504-418TAA1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EDAC:](#)

[14K-504-418TAA1](#)