


TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①



SPECIFICATION:

MATERIAL:

CONTACT: BRASS GOLD FLASH PLATING ALL OVER NICKEL UNDERPLATING
HOUSING : PA, BLACK

ELECTRICAL:

RATED VOLTAGE (PER CONTACT): 24V
RATED CURRENT (PER CONTACT): 3A
INSULATION RESISTANCE: 100MEGAOHMS MINIMUM
CONTACT RESISTANCE: 25mOHMS MAXIMUM
WORKING TEMPERATURE RANGE: -30°C~+85°C



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

MAGNETIC SPRING LOADED CONNECTOR, 31POS, MALE

ACAD REFERENCE NO.: 685A3131260111E		UNIT: MM
DRAWN: J.L.	DATE: 2023-04-25	
CHECKED: R.S.M	DATE: 2023-04-25	
SCALE: (IN CAD 1:1)	SHEET 1 OF 1	
DRAWING NUMBER: 685A3131260111E	ISSUE	
PART NUMBER: 685A3131260111E	1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

[685A3131260111E](#)