



SERIES 570



FEATURES

- Fully Waterproof connector
- Plastic latch provides locking mechanism and polarity
- 5.8mm Contact Spacing
- Plug and Receptacle in 2 or 3 Contact positions
- Board Mount Style available in 1, 2, or 3 contact positions
- Contact Termination Options include Crimp and P.C Tail
- Tools Available for Contact Installation, Removal and Crimping
- Able to carry large current up to 10 A

SPECIFICATIONS

- Insulator Material: PBT (UL 94V-0)
- Contact Material: Brass / Tin plating
- Wire Housing Seal: Silicone Rubber
- Current Rating: 10 Amperies maximum
- Contact Resistance: 10 m Ω maximum
- Insulator Withstanding Voltage: 1700 V AC rms at Sea Level
- Insulation Resistance: 1000 M Ω minmum at 500 VDC
- Operating Temperature: -40 to +105 Degrees C
- Rather Voltage: 300V
- Waterproof Grade 4
- For use with PC boards up to (.063") 1.6mm

Example Part Number 570 - 003 - 000 - 1 0 0

Series _____
Total Number of Contacts _____
Contact Code _____
Style _____
Wire Diameter _____
Termination _____

Series 570

Total Number of Contacts 001, 002, 003

Contact Code

000 No Contacts Assembled
420 Board Mount Contact Installed

Style

1 Plug
2 Receptacle

Wire Diameter

0 None Installed; both contacts and water seals sold seperately

Termination

0 Wire Crimp terminals required
1 PC Board Mount

Ordering Code Notes

- 1) Crimp contacts are available for 565 series connectors
Contacts may be ordered seperate for pre-wired or select position assembly

Part Number

570-290-711
570-290-721
570-290-731
570-290-741

Description

Male Contact for smaller gauge wire
Female Contact for smaller gauge wire
Male Contact for larger gauge wire
Female Contact for larger gauge wire

- 2) Insulator design prevents improper mating of individual plug and receptacle

- 3) Wire Seals are available as follows:

Part Number	Colour	Insulation Dia	Flange
570-260-001	Black	.067" (1.7) to .075" (2.1)	No
570-260-002	Blue	.079" (2.1) to .102" (2.7)	No
570-260-003	Blue	.083" (2.1) to .106" (2.7)	Yes
570-260-004	Brown	.106" (2.7) to .122" (3.1)	Yes

PCB Header

570-001-420-101
570-002-420-101
570-003-420-101

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EDAC:](#)

[570-290-741](#) [570-290-731](#) [570-002-744-200](#) [570-002-735-100](#) [570-260-002](#) [570-001-744-200](#) [570-003-734-100](#)
[570-003-744-200](#) [570-002-734-100](#) [570-280-300](#) [570-003-735-100](#) [570-002-745-200](#)