




ORIGINAL

ADD DAUGHTER BOARD RECOMMENDATION (2)
R.STA.MONICA AUG.11/2015



- 1- CONTACT MATERIAL: PHOSPHOR BRONZE
- 2- INSULATOR MATERIAL: GREEN DIALLYL PHTHALATE, UL 94V-0
- 3- CONTACT PLATING: GOLD OVER NICKEL ALL OVER
- 4- CURRENT RATING: 5 AMPERES.
- 5- CONTACT RESISTANCE: 10 MILLIOHMS MAXIMUM.
- 5- INSULATION RESISTANCE: 5000 MEGOHMS MINIMUM.
- 6- DIELECTRIC WITHSTANDING VOLTAGE: 1800 VAC RMS
AT SEE LEVEL.
- 7- INSERTION AND WITHDRAWAL FORCES: 16oz AND 1oz
RESPECTIVELY PER CONTACT PAIR
- 8- OPERATING TEMPERATURE: -65°C TO +125°C



368 SERIES CARD EDGE R/ANGLE CONNECTOR
 .156(3.96) CONTACT SPACING (CENTER MODULE)



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
SHALL NOT BE REPRODUCED,OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

REF. 368-006-540-201

DRAWN: F.BRIONES

DATE: JUL. 21/10

PART NUMBER

368-006-540-201

DRAWING NUMBER

368-006-540-201

ISSUE

2



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

[368-006-540-201](#)