




MATERIALS:

INSULATOR : PBT COLOR BLACK, UL 94V-0 RATING
CONTACTS: PHOSPHOR BRONZE, .30u" OF GOLD PLATED
ON CONTACT AREA, TIN/LEAD ON TAILS OVER NICKEL
SHELL: STEEL, NICKEL PLATED

ELECTRICAL SPECIFICATIONS

CONTACT CURRENT RATING: 1 AMPERE
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC rms
INSULATION RESISTANCE:
1000 MEGOHMS MIN. AT 500 VDC
CONTACT RESISTANCE: 30 MILLIOHMS MAX.
OPERATING TEMPERATURE: -55°C TO +105°C



50 POSITION MINIATURE RIBBON PLUG
RIGHT ANGLE P.C.B.

ACAD REFERENCE NO.	B57-150-261-201
DRAWN: F.JAWDI	DATE: OCT.22/02
CHECKED:	DATE:



EDAC INC
TORONTO, ONTARIO
CANADA

CONNECTOR PART NO. B57-150-261-201

SCALE: IN C.A.D. 1:1	SHEET 1 OF 1
DRAWING NUMBER	
B57-150-261-201	ISSUE 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EDAC:](#)

[B57-150-261-201](#)