



TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.35
.XX	±0.25
.XXX	±0.15

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.
UNLESS OTHERWISE SPECIFIED, ALL RADIUS ARE 0.2 MM.




ISSUE NUMBER	1
ORIGINAL	




NOTES:

MATERIAL: LCP+30% GLASS REINFORCED, UL94V-0
HOUSING: PHOSPHOR BRONZE
SHIELD: NICKEL PLATING
CONTACT: PHOSPHOR BRONZE
GOLD FLASH PLATING ON CONTACT AREA
MATTE TIN PLATING 30~100μ" ON SOLDER
TAIL OVER NICKEL 50~150μ" UNDER PLATING

PCB HOLE DIM:
DRILLED HOLE = 0.700±0.025mm
FINISHED HOLE = 0.600±0.050mm
Cu THICKNESS = 0.0375±0.0125mm
SnPb THICKNESS = 0.007±0.003mm



ALL PLATED THRU HOLES
SCALE 2:1



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ZD CONNECTOR, MALE, VERTICAL, 2 PAIR		ACAD REFERENCE NO.: 500-040-231-C01	
		DRAWN: W.T	DATE: JUNE.27 /2018
<div>EDAC INC</div> <div>TORONTO, ONTARIO</div> <div>CANADA</div> <div>YOUR CONNECTION TO QUALITY & SERVICE</div>	<div>THESE DRAWINGS AND SPECIFICATIONS</div> <div>ARE THE PROPERTY OF EDAC INC., AND</div> <div>SHALL NOT BE REPRODUCED, OR COPIED</div> <div>OR USED AS THE BASIS FOR THE</div> <div>MANUFACTURE OR SALE OF APPARATUS</div> <div>WITHOUT WRITTEN PERMISSION.</div>	CHECKED:	DATE:
		SCALE: N.T.S	SHEET 1 OF 1
		DRAWING NUMBER: 500-040-231-C01	ISSUE
		PART NUMBER: 500-040-231-C01	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

[500-040-231-C01](#)