

PA56TS48DD-WO

SPANSION S29GL512M

TSOP56		DIP48	DIP48	TSOP56	
3	A15	1	48	A16	54
4	A14	2	47	A24	56
5	A13	3	46	A22	2
6	A12	4	45	DQ15/A-1	51
7	A11	5	44	DQ7	50
8	A10	6	43	DQ14	49
9	A9	7	42	DQ6	48
10	A8	8	41	DQ13	47
11	A19	9	40	DQ5	46
12	A20	10	39	DQ12	45
13	WE#	11	38	DQ4	44
14	RESET#	12	37	* Note 2	
15	A21	13	36	DQ11	42
16	WP#/ACC	14	35	DQ3	41
1	A23	15	34	DQ10	40
18	A18	16	33	DQ2	39
19	A17	17	32	DQ9	38
20	A7	18	31	DQ1	37
21	A6	19	30	DQ8	36
22	A5	20	29	DQ0	35
23	A4	21	28	OE#	34
24	A3	22	27	* Note 1	
25	A2	23	26	CE#	32
26	A1	24	25	A0	31

* Note 1 (GND)

DIP48 - 27

TSOP56 - 33(Vss), 52(Vss)

* Note 2 (VCC)

DIP48 - 37

TSOP56 - 17(RY/BY#), 43(Vcc), 29(Vio), 53(BYTE#)

PA56TS48DD-WO PartList

SPANSION S29GL512M

1.	TOP Board	:	PA56TS48DB_C_D-WO-TOP REV2.0
	BOT Board	:	48 DIP TYPE A
	Socket P/N	:	648-0562211-A01
	C1	:	0.1uF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EETools:](#)

[PA56TS48DD](#)