




**ELECTROSWITCH**UNIT OF ELECTRO SWITCH CORP.
WEYMOUTH MASSACHUSETTS 02188
TEL(781)335-5200 FAX(781)335-4253**SERIES 24 HIGH SPEED
ELECTRIC RESET
LOCKOUT RELAY****7835DD**(3) #10-32 X .56
MOUNTING SCREWS
SUPPLIEDSPECIAL
AUTO TRIP/MANUAL RESET
TARGET NAMEPLATE

TRIP RESPONSE TIME - 8 ms (MAX)

COIL SPECIFICATIONS	TRIP	RESET
NOMINAL VOLTAGE:	125 VDC	125 VDC
OPERATING RANGE(VDC):	30-140	100-140
THRESHOLD (MIN):	16 VDC	N/A
COIL RESISTANCE:	27 Ω	12.4 Ω
COIL BURDEN (125 VDC):	4.6 AMP	10.1 AMP




UL RECOGNIZED CONTACT RATINGS	
20A-120VAC	3A-125VDC
15A-240VAC	1A-250VDC
6A-600VAC	

FOR FURTHER INFORMATION
REFER TO TECHNICAL PUBLICATION
LOR-1STANDARD
NAMEPLATE ENGRAVING

CODE 00N-0L13

**TYPICAL CONTACT
DECK LAYOUT**

CONTACTS	POSITION	
	TRIP	RESET
DECK 1		
11	X	
12		X
15		X
14	X	

ADDITIONAL CONTACT
DECKS SAME AS DECK 1
EXCEPT TERMINAL NUMBERS
(DECK 2: 21 TO 28,
DECK 3: 31 TO 38 ETC.)**PANEL DRILLING
DIMENSIONS****CONTROL CIRCUIT**

CONTACTS	POSITION	
	TRIP	RESET
CONTROL DECK		
F	X	
A		X

MADE BY: J.F.R. DATE: 6/3/86
APPR BY: J.R. DATE: 6/3/86DWG. NO:
SHEET 1 OF 1REV
DREV 27982
D ECN 23464
C ECN 21066
B ECN 20436
A ECN 20436
WCK 5/3/05
GHP DC 6/27/96
JR WDS 12/17/93
JR WDS 2/8/93

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Electroswitch:](#)

[7835DD](#)