



FOOT SWITCH


SPECIFICATION

Rating:	DC9V; 1A
Contact Resistance:	Initial:<30 mΩ, after test: <100 mΩ
Insulation Resistance:	Initial: >100 mΩ, after humidity test: >50 mΩ
Withstand Voltage:	500V AC (50-60 Hz, 2 mA)-1minute
Operating Force:	Initial: 3.0±0.8 kgf, after durability test: 3.0±1.0 kgf
Life Cycle:	30,000 cycles
Size(mm):	As following drawings

SF17010F-0302-21R-L




SF17020F-0302-21R-L



SPECIFICATION

Operating Force:	650±200 gf.cm
Life Cycle:	20,000 cycles
Size(mm) :	As following drawings

SF12030F



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha \(Taiwan\):](#)

[SF17020F-0302-21R-L](#) [SF17010F-0302-21R-L](#) [SF12030F](#) [SF17020F-0302-21R-L-015](#) [SF12030F-038](#) [SF17010F-0302-21R-L-011](#)