

Certificate of Compliance

We certify that the product listed below is in compliance with the Directive 2011/65/EU and (EU)2015/863 of the European Parliament, and of the Council on the restriction of the use of certain hazardous substances in electrical and electronics equipment. (1 July 2011, RoHS Directive)

Product model	Exemption
SG-8018CA	No Exemption

The restricted substances referred to in the RoHS Directives (EU) 2015/863 are as listed below.

Substance	Maximum concentration values tolerated by weight in homogeneous materials.
Lead (Pb)	0.1% (1000 ppm)
Mercury (Hg)	0.1% (1000 ppm)
Cadmium (Cd)	0.01% (100 ppm)
Hexavalent chromium (Cr 6+)	0.1% (1000 ppm)
Polybrominated biphenyls (PBB)	0.1% (1000 ppm)
Polybrominated diphenyl ethers (PBDE)	0.1% (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% (1000 ppm)
Dibutyl phthalate (DBP)	0.1% (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% (1000 ppm)

Company name: SEIKO EPSON CORPORATION

Company Address: 8548 Nakaminowa, Minowa-machi, Kamiina-gun,
Nagano-ken, 399-4696 JAPAN

Signature:



Name(Title): Yasushi Hiraizumi
(General Manager / TD CS Quality Assurance Department)

Issue Date: July 30, 2021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Epson:

[SG-8018CA 0.751234M-TJHPA0](#) [SG-8018CA 0.751234M-TJHSA0](#) [SG-8018CA 0.7715M-TJHPA0](#) [SG-8018CA 0.7715M-TJHSA0](#) [SG-8018CA 0.7840M-TJHPA0](#) [SG-8018CA 0.7840M-TJHSA0](#) [SG-8018CA 99.9960M-TJHPA0](#) [SG-8018CA 99.9960M-TJHSA0](#) [SG-8018CA 99.9980M-TJHPA0](#) [SG-8018CA 99.9980M-TJHSA0](#) [SG-8018CA 99.9900M-TJHPA0](#) [SG-8018CA 99.9900M-TJHSA0](#) [SG-8018CA 99.9925M-TJHPA0](#) [SG-8018CA 99.9925M-TJHSA0](#) [SG-8018CA 99.9950M-TJHPA0](#) [SG-8018CA 99.9950M-TJHSA0](#) [SG-8018CA 99.7500M-TJHPA0](#) [SG-8018CA 99.7500M-TJHSA0](#) [SG-8018CA 99.751230M-TJHPA0](#) [SG-8018CA 99.751230M-TJHSA0](#) [SG-8018CA 99.9300M-TJHPA0](#) [SG-8018CA 99.9300M-TJHSA0](#) [SG-8018CA 99.5328M-TJHPA0](#) [SG-8018CA 99.5328M-TJHSA0](#) [SG-8018CA 99.6923M-TJHPA0](#) [SG-8018CA 99.6923M-TJHSA0](#) [SG-8018CA 99.7200M-TJHPA0](#) [SG-8018CA 99.7200M-TJHSA0](#) [SG-8018CA 98.7650M-TJHPA0](#) [SG-8018CA 98.7650M-TJHSA0](#) [SG-8018CA 99.1440M-TJHPA0](#) [SG-8018CA 99.1440M-TJHSA0](#) [SG-8018CA 99.3000M-TJHPA0](#) [SG-8018CA 99.3000M-TJHSA0](#) [SG-8018CA 97.5000M-TJHPA0](#) [SG-8018CA 97.5000M-TJHSA0](#) [SG-8018CA 98.0000M-TJHPA0](#) [SG-8018CA 98.0000M-TJHSA0](#) [SG-8018CA 98.2800M-TJHPA0](#) [SG-8018CA 98.2800M-TJHSA0](#) [SG-8018CA 97.0000M-TJHPA0](#) [SG-8018CA 97.0000M-TJHSA0](#) [SG-8018CA 97.030887M-TJHPA0](#) [SG-8018CA 97.030887M-TJHSA0](#) [SG-8018CA 97.2000M-TJHPA0](#) [SG-8018CA 97.2000M-TJHSA0](#) [SG-8018CA 95.6250M-TJHPA0](#) [SG-8018CA 95.6250M-TJHSA0](#) [SG-8018CA 95.646241M-TJHPA0](#) [SG-8018CA 95.646241M-TJHSA0](#) [SG-8018CA 96.7680M-TJHPA0](#) [SG-8018CA 96.7680M-TJHSA0](#) [SG-8018CA 93.7500M-TJHPA0](#) [SG-8018CA 93.7500M-TJHSA0](#) [SG-8018CA 94.0000M-TJHPA0](#) [SG-8018CA 94.0000M-TJHSA0](#) [SG-8018CA 95.5730M-TJHPA0](#) [SG-8018CA 95.5730M-TJHSA0](#) [SG-8018CA 93.3300M-TJHPA0](#) [SG-8018CA 93.3300M-TJHSA0](#) [SG-8018CA 93.3333M-TJHPA0](#) [SG-8018CA 93.3333M-TJHSA0](#) [SG-8018CA 93.4400M-TJHPA0](#) [SG-8018CA 93.4400M-TJHSA0](#) [SG-8018CA 93.0000M-TJHPA0](#) [SG-8018CA 93.0000M-TJHSA0](#) [SG-8018CA 93.3000M-TJHPA0](#) [SG-8018CA 93.3000M-TJHSA0](#) [SG-8018CA 93.3120M-TJHPA0](#) [SG-8018CA 93.3120M-TJHSA0](#) [SG-8018CA 92.5000M-TJHPA0](#) [SG-8018CA 92.5000M-TJHSA0](#) [SG-8018CA 92.8571M-TJHPA0](#) [SG-8018CA 92.8571M-TJHSA0](#) [SG-8018CA 92.9000M-TJHPA0](#) [SG-8018CA 92.9000M-TJHSA0](#) [SG-8018CA 91.8750M-TJHPA0](#) [SG-8018CA 91.8750M-TJHSA0](#) [SG-8018CA 92.0000M-TJHPA0](#) [SG-8018CA 92.0000M-TJHSA0](#) [SG-8018CA 92.4000M-TJHPA0](#) [SG-8018CA 92.4000M-TJHSA0](#) [SG-8018CA 91.0000M-TJHPA0](#) [SG-8018CA 91.0000M-TJHSA0](#) [SG-8018CA 91.4000M-TJHPA0](#) [SG-8018CA 91.4000M-TJHSA0](#) [SG-8018CA 91.7500M-TJHPA0](#) [SG-8018CA 91.7500M-TJHSA0](#) [SG-8018CA 90.3168M-TJHPA0](#) [SG-8018CA 90.3168M-TJHSA0](#) [SG-8018CA 90.3186M-TJHPA0](#) [SG-8018CA 90.3186M-TJHSA0](#) [SG-8018CA 90.9090M-TJHPA0](#) [SG-8018CA 90.9090M-TJHSA0](#) [SG-8018CA 9.931250M-TJHPA0](#) [SG-8018CA 9.931250M-TJHSA0](#) [SG-8018CA 9.961250M-TJHPA0](#) [SG-8018CA 9.961250M-TJHSA0](#) [SG-8018CA 9.9840M-TJHPA0](#) [SG-8018CA 9.9840M-TJHSA0](#)