

Certificate of Compliance

We certify that the product listed below is in compliance with the Directive 2011/65/EU and (EU)2015/863 of the European Parliament, and of the Council on the restriction of the use of certain hazardous substances in electrical and electronics equipment. (1 July 2011, RoHS Directive)

Product model	Exemption
SG-8018CB	No Exemption

The restricted substances referred to in the RoHS Directives (EU) 2015/863 are as listed below.

Substance	Maximum concentration values tolerated by weight in homogeneous materials.
Lead (Pb)	0.1% (1000 ppm)
Mercury (Hg)	0.1% (1000 ppm)
Cadmium (Cd)	0.01% (100 ppm)
Hexavalent chromium (Cr 6+)	0.1% (1000 ppm)
Polybrominated biphenyls (PBB)	0.1% (1000 ppm)
Polybrominated diphenyl ethers (PBDE)	0.1% (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% (1000 ppm)
Butyl benzyl phthalate (BBP)	0.1% (1000 ppm)
Dibutyl phthalate (DBP)	0.1% (1000 ppm)
Diisobutyl phthalate (DIBP)	0.1% (1000 ppm)

Company name: SEIKO EPSON CORPORATION

Company Address: 8548 Nakaminowa, Minowa-machi, Kamiina-gun,
Nagano-ken, 399-4696 JAPAN

Signature:



Name(Title):

Yasushi Hiraizumi
(General Manager / TD CS Quality Assurance Department)

Issue Date:

July 30, 2021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Epson:

[SG-8018CB 11.0590M-TJHPA0](#) [SG-8018CB 11.0590M-TJHSA0](#) [SG-8018CB 11.059920M-TJHPA0](#) [SG-8018CB 11.059920M-TJHSA0](#) [SG-8018CB 11.060472M-TJHPA0](#) [SG-8018CB 11.060472M-TJHSA0](#) [SG-8018CB 11.0670M-TJHPA0](#) [SG-8018CB 11.0670M-TJHSA0](#) [SG-8018CB 11.0896M-TJHPA0](#) [SG-8018CB 11.0896M-TJHSA0](#) [SG-8018CB 11.1100M-TJHPA0](#) [SG-8018CB 11.1100M-TJHSA0](#) [SG-8018CB 11.1300M-TJHPA0](#) [SG-8018CB 11.1300M-TJHSA0](#) [SG-8018CB 11.1550M-TJHPA0](#) [SG-8018CB 11.1550M-TJHSA0](#) [SG-8018CB 11.2280M-TJHPA0](#) [SG-8018CB 11.2280M-TJHSA0](#) [SG-8018CB 11.288460M-TJHPA0](#) [SG-8018CB 11.288460M-TJHSA0](#) [SG-8018CB 11.2941M-TJHPA0](#) [SG-8018CB 11.2941M-TJHSA0](#) [SG-8018CB 11.2986M-TJHPA0](#) [SG-8018CB 11.2986M-TJHSA0](#) [SG-8018CB 11.3541M-TJHPA0](#) [SG-8018CB 11.3541M-TJHSA0](#) [SG-8018CB 11.3920M-TJHPA0](#) [SG-8018CB 11.3920M-TJHSA0](#) [SG-8018CB 11.527848M-TJHPA0](#) [SG-8018CB 11.527848M-TJHSA0](#) [SG-8018CB 11.6640M-TJHPA0](#) [SG-8018CB 11.6640M-TJHSA0](#) [SG-8018CB 11.703880M-TJHPA0](#) [SG-8018CB 11.703880M-TJHSA0](#) [SG-8018CB 11.9450M-TJHPA0](#) [SG-8018CB 11.9450M-TJHSA0](#) [SG-8018CB 11.9550M-TJHPA0](#) [SG-8018CB 11.9550M-TJHSA0](#) [SG-8018CB 11.9808M-TJHPA0](#) [SG-8018CB 11.9808M-TJHSA0](#) [SG-8018CB 11.981350M-TJHPA0](#) [SG-8018CB 11.981350M-TJHSA0](#) [SG-8018CB 11.9850M-TJHPA0](#) [SG-8018CB 11.9850M-TJHSA0](#) [SG-8018CB 11.9990M-TJHPA0](#) [SG-8018CB 11.9990M-TJHSA0](#) [SG-8018CB 110.5400M-TJHPA0](#) [SG-8018CB 110.5400M-TJHSA0](#) [SG-8018CB 111.0000M-TJHPA0](#) [SG-8018CB 111.0000M-TJHSA0](#) [SG-8018CB 111.1110M-TJHPA0](#) [SG-8018CB 111.1110M-TJHSA0](#) [SG-8018CB 111.154120M-TJHPA0](#) [SG-8018CB 111.154120M-TJHSA0](#) [SG-8018CB 111.3750M-TJHPA0](#) [SG-8018CB 111.3750M-TJHSA0](#) [SG-8018CB 112.1200M-TJHPA0](#) [SG-8018CB 112.1200M-TJHSA0](#) [SG-8018CB 112.1920M-TJHPA0](#) [SG-8018CB 112.1920M-TJHSA0](#) [SG-8018CB 112.2400M-TJHPA0](#) [SG-8018CB 112.2400M-TJHSA0](#) [SG-8018CB 112.3100M-TJHPA0](#) [SG-8018CB 112.3100M-TJHSA0](#) [SG-8018CB 112.4100M-TJHPA0](#) [SG-8018CB 112.4100M-TJHSA0](#) [SG-8018CB 112.4400M-TJHPA0](#) [SG-8018CB 112.4400M-TJHSA0](#) [SG-8018CB 112.4800M-TJHPA0](#) [SG-8018CB 112.4800M-TJHSA0](#) [SG-8018CB 112.5000M-TJHPA0](#) [SG-8018CB 112.5000M-TJHSA0](#) [SG-8018CB 112.6400M-TJHPA0](#) [SG-8018CB 112.6400M-TJHSA0](#) [SG-8018CB 113.333333M-TJHPA0](#) [SG-8018CB 113.333333M-TJHSA0](#) [SG-8018CB 113.7500M-TJHPA0](#) [SG-8018CB 113.7500M-TJHSA0](#) [SG-8018CB 114.0480M-TJHPA0](#) [SG-8018CB 114.0480M-TJHSA0](#) [SG-8018CB 114.2150M-TJHPA0](#) [SG-8018CB 114.2150M-TJHSA0](#) [SG-8018CB 114.2850M-TJHPA0](#) [SG-8018CB 114.2850M-TJHSA0](#) [SG-8018CB 114.2885M-TJHPA0](#) [SG-8018CB 114.2885M-TJHSA0](#) [SG-8018CB 114.2900M-TJHPA0](#) [SG-8018CB 114.2900M-TJHSA0](#) [SG-8018CB 114.5440M-TJHPA0](#) [SG-8018CB 114.5440M-TJHSA0](#) [SG-8018CB 114.5600M-TJHPA0](#) [SG-8018CB 114.5600M-TJHSA0](#) [SG-8018CB 114.775489M-TJHPA0](#) [SG-8018CB 114.775489M-TJHSA0](#) [SG-8018CB 115.4400M-TJHPA0](#) [SG-8018CB 115.4400M-TJHSA0](#) [SG-8018CB 115.981982M-TJHPA0](#) [SG-8018CB 115.981982M-TJHSA0](#)

TJHSA0 SG-8018CB 116.0000M-TJHPA0 SG-8018CB 116.0000M-TJHSA0