

## Certificate of Compliance

We certify that the product listed below is in compliance with the Directive 2011/65/EU and (EU)2015/863 of the European Parliament, and of the Council on the restriction of the use of certain hazardous substances in electrical and electronics equipment. (1 July 2011, RoHS Directive)

| Product model | Exemption    |
|---------------|--------------|
| SG-8018CE     | No Exemption |

The restricted substances referred to in the RoHS Directives (EU) 2015/863 are as listed below.

| Substance                             | Maximum concentration values tolerated by weight in homogeneous materials. |
|---------------------------------------|----------------------------------------------------------------------------|
| Lead (Pb)                             | 0.1% (1000 ppm)                                                            |
| Mercury (Hg)                          | 0.1% (1000 ppm)                                                            |
| Cadmium (Cd)                          | 0.01% (100 ppm)                                                            |
| Hexavalent chromium (Cr 6+)           | 0.1% (1000 ppm)                                                            |
| Polybrominated biphenyls (PBB)        | 0.1% (1000 ppm)                                                            |
| Polybrominated diphenyl ethers (PBDE) | 0.1% (1000 ppm)                                                            |
| Bis(2-ethylhexyl) phthalate (DEHP)    | 0.1% (1000 ppm)                                                            |
| Butyl benzyl phthalate (BBP)          | 0.1% (1000 ppm)                                                            |
| Dibutyl phthalate (DBP)               | 0.1% (1000 ppm)                                                            |
| Diisobutyl phthalate (DIBP)           | 0.1% (1000 ppm)                                                            |

**Company name:** SEIKO EPSON CORPORATION

**Company Address:** 8548 Nakaminowa, Minowa-machi, Kamiina-gun,  
Nagano-ken, 399-4696 JAPAN

**Signature:**



**Name(Title):**

Yasushi Hiraizumi  
(General Manager / TD CS Quality Assurance Department)

**Issue Date:**

July 30, 2021

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Epson:

[SG-8018CE 11.0590M-TJHPA0](#) [SG-8018CE 11.0590M-TJHSA0](#) [SG-8018CE 11.059920M-TJHPA0](#) [SG-8018CE 11.059920M-TJHSA0](#) [SG-8018CE 11.060472M-TJHPA0](#) [SG-8018CE 11.060472M-TJHSA0](#) [SG-8018CE 11.0670M-TJHPA0](#) [SG-8018CE 11.0670M-TJHSA0](#) [SG-8018CE 11.0896M-TJHPA0](#) [SG-8018CE 11.0896M-TJHSA0](#) [SG-8018CE 11.1100M-TJHPA0](#) [SG-8018CE 11.1100M-TJHSA0](#) [SG-8018CE 11.1300M-TJHPA0](#) [SG-8018CE 11.1300M-TJHSA0](#) [SG-8018CE 11.1550M-TJHPA0](#) [SG-8018CE 11.1550M-TJHSA0](#) [SG-8018CE 11.2280M-TJHPA0](#) [SG-8018CE 11.2280M-TJHSA0](#) [SG-8018CE 11.288460M-TJHPA0](#) [SG-8018CE 11.288460M-TJHSA0](#) [SG-8018CE 11.2941M-TJHPA0](#) [SG-8018CE 11.2941M-TJHSA0](#) [SG-8018CE 11.2986M-TJHPA0](#) [SG-8018CE 11.2986M-TJHSA0](#) [SG-8018CE 11.3541M-TJHPA0](#) [SG-8018CE 11.3541M-TJHSA0](#) [SG-8018CE 11.3920M-TJHPA0](#) [SG-8018CE 11.3920M-TJHSA0](#) [SG-8018CE 11.527848M-TJHPA0](#) [SG-8018CE 11.527848M-TJHSA0](#) [SG-8018CE 11.6640M-TJHPA0](#) [SG-8018CE 11.6640M-TJHSA0](#) [SG-8018CE 11.703880M-TJHPA0](#) [SG-8018CE 11.703880M-TJHSA0](#) [SG-8018CE 11.9450M-TJHPA0](#) [SG-8018CE 11.9450M-TJHSA0](#) [SG-8018CE 11.9550M-TJHPA0](#) [SG-8018CE 11.9550M-TJHSA0](#) [SG-8018CE 11.9808M-TJHPA0](#) [SG-8018CE 11.9808M-TJHSA0](#) [SG-8018CE 11.981350M-TJHPA0](#) [SG-8018CE 11.981350M-TJHSA0](#) [SG-8018CE 11.9850M-TJHPA0](#) [SG-8018CE 11.9850M-TJHSA0](#) [SG-8018CE 11.9990M-TJHPA0](#) [SG-8018CE 11.9990M-TJHSA0](#) [SG-8018CE 110.5400M-TJHPA0](#) [SG-8018CE 110.5400M-TJHSA0](#) [SG-8018CE 111.0000M-TJHPA0](#) [SG-8018CE 111.0000M-TJHSA0](#) [SG-8018CE 111.1110M-TJHPA0](#) [SG-8018CE 111.1110M-TJHSA0](#) [SG-8018CE 111.154120M-TJHPA0](#) [SG-8018CE 111.154120M-TJHSA0](#) [SG-8018CE 111.3750M-TJHPA0](#) [SG-8018CE 111.3750M-TJHSA0](#) [SG-8018CE 112.1200M-TJHPA0](#) [SG-8018CE 112.1200M-TJHSA0](#) [SG-8018CE 112.1920M-TJHPA0](#) [SG-8018CE 112.1920M-TJHSA0](#) [SG-8018CE 112.2400M-TJHPA0](#) [SG-8018CE 112.2400M-TJHSA0](#) [SG-8018CE 112.3100M-TJHPA0](#) [SG-8018CE 112.3100M-TJHSA0](#) [SG-8018CE 112.4100M-TJHPA0](#) [SG-8018CE 112.4100M-TJHSA0](#) [SG-8018CE 112.4400M-TJHPA0](#) [SG-8018CE 112.4400M-TJHSA0](#) [SG-8018CE 112.4800M-TJHPA0](#) [SG-8018CE 112.4800M-TJHSA0](#) [SG-8018CE 112.5000M-TJHPA0](#) [SG-8018CE 112.5000M-TJHSA0](#) [SG-8018CE 112.6400M-TJHPA0](#) [SG-8018CE 112.6400M-TJHSA0](#) [SG-8018CE 113.333333M-TJHPA0](#) [SG-8018CE 113.333333M-TJHSA0](#) [SG-8018CE 113.7500M-TJHPA0](#) [SG-8018CE 113.7500M-TJHSA0](#) [SG-8018CE 114.0480M-TJHPA0](#) [SG-8018CE 114.0480M-TJHSA0](#) [SG-8018CE 114.2150M-TJHPA0](#) [SG-8018CE 114.2150M-TJHSA0](#) [SG-8018CE 114.2850M-TJHPA0](#) [SG-8018CE 114.2850M-TJHSA0](#) [SG-8018CE 114.2885M-TJHPA0](#) [SG-8018CE 114.2885M-TJHSA0](#) [SG-8018CE 114.2900M-TJHPA0](#) [SG-8018CE 114.2900M-TJHSA0](#) [SG-8018CE 114.5440M-TJHPA0](#) [SG-8018CE 114.5440M-TJHSA0](#) [SG-8018CE 114.5600M-TJHPA0](#) [SG-8018CE 114.5600M-TJHSA0](#) [SG-8018CE 114.775489M-TJHPA0](#) [SG-8018CE 114.775489M-TJHSA0](#) [SG-8018CE 115.4400M-TJHPA0](#) [SG-8018CE 115.4400M-TJHSA0](#) [SG-8018CE 115.981982M-TJHPA0](#) [SG-8018CE 115.981982M-TJHSA0](#)

TJHSA0 SG-8018CE 116.0000M-TJHPA0 SG-8018CE 116.0000M-TJHSA0