

SINGLEMODE FIBER MATING ADAPTER PANEL, LGX FOOTPRINT, 6CT, SCUPC

GENERAL PRODUCT SPECIFICATIONS

Mfg. Part Number:	AP-LGX-SCU-BL-6
Mfg. Part Name:	Fiber Adapter Panel, Mating Adapter Panel, LGX Footprint, SM, 6ct, SCUPC
	SCUPC Zirconia Ceramic
Fiber Count:	6
Jacket/Cable Color	Black ABS Plastic Filament
Dimensions	5.1" W x 1.13" H

TECHNICAL SPECIFICATIONS

Mating Durability	800-1,000 Cycles
Wavelength (Maximum – Minimum)	1280nm, 1640nm
Typical Wavelength Usage	1310nm, 1550nm
Glass Mode	Singlemode 9/125um

PHYSICAL DIMENSIONS & PROPERTIES

Product Weight	5 ounces
Product Packaging	8" x 10" Bag
Recommended Storage Temperature Range (Celsius)	-40 to 85 C
Recommended Operating Temperature Range (Celsius)	-20 to 70 C
Moisture Sensitivity Level (MSL)	1 (Unlimited)
Is this part static sensitive?	NO
Is this part lead free?	YES
Is this part RoHS compliant?	YES
Country of Origin	US
ECCN	5A001.c

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Megladon Manufacturing:](#)

[AP-LGX-SCU-BL-6](#)