

SINGLEMODE FIBER MATING ADAPTER PANEL, LGX FOOTPRINT, 6CT, STUPC

GENERAL PRODUCT SPECIFICATIONS

| | |
|---------------------------|--|
| Mfg. Part Number: | AP-LGX-STU-BL-6 |
| Mfg. Part Name: | Fiber Adapter Panel, Mating Adapter Panel, LGX Footprint, SM, 6ct, STUPC |
| | STUPC Zirconia Ceramic |
| Fiber Count: | 6 |
| Jacket/Cable Color | Black ABS Plastic Filament |
| Dimensions | 5.1" W x 1.13" H |

TECHNICAL SPECIFICATIONS

| | |
|--------------------------------|--------------------|
| Maximum Insertion Loss (dB) | ≤0.1 |
| Maximum Return Loss (dB) | |
| Mating Durability | 800-1,000 Cycles |
| Wavelength (Maximum – Minimum) | 1280nm, 1640nm |
| Typical Wavelength Usage | 1310nm, 1550nm |
| Glass Mode | Singlemode 9/125um |

PHYSICAL DIMENSIONS & PROPERTIES

| | |
|---|---------------|
| Product Weight | 8 ounces |
| Product Packaging | 8" x 10" Bag |
| Recommended Storage Temperature Range (Celsius) | -40 to 85 C |
| Recommended Operating Temperature Range (Celsius) | -20 to 70 C |
| Moisture Sensitivity Level (MSL) | 1 (Unlimited) |
| Is this part static sensitive? | NO |
| Is this part lead free? | YES |
| Is this part RoHS compliant? | YES |
| Country of Origin | US |
| ECCN | 5A001.c |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Megladon Manufacturing:](#)

[AP-LGX-STU-BL-6](#)