

## FIBER ADAPTER PANEL, MATING ADAPTER PANEL, PANDUIT FOOTPRINT, SM, 6CT, STUPC

## GENERAL PRODUCT SPECIFICATIONS

<b>Mfg. Part Number:</b>	AP-PAN-STU-BL-6
<b>Mfg. Part Name:</b>	Fiber Adapter Panel, Mating Adapter Panel, Panduit Footprint, SM, 6ct, STUPC
<b>Connector:</b>	STUPC
<b>Adapter Type:</b>	Zirconia Ceramic
<b>Fiber Count:</b>	6
<b>Jacket/Cable Color</b>	Black ABS Plastic Filament
<b>Dimensions</b>	4.3" W x 1.39" H

## TECHNICAL SPECIFICATIONS

Mating Durability	800-1,000 Cycles
Wavelength (Maximum – Minimum)	1280nm, 1640nm
Typical Wavelength Usage	1310nm, 1550nm
Glass Mode	Singlemode 9/125um

## PHYSICAL DIMENSIONS &amp; PROPERTIES

Product Weight	8 ounces
Product Packaging	8" x 10" Bag
Recommended Storage Temperature Range (Celsius)	-40 to 85 C
Recommended Operating Temperature Range (Celsius)	-20 to 70 C
Moisture Sensitivity Level (MSL)	1 (Unlimited)
Is this part static sensitive?	NO
Is this part lead free?	YES
Is this part RoHS compliant?	YES
Country of Origin	US
ECCN	5A001.c

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Megladon Manufacturing:](#)

[AP-PAN-STU-BL-6](#)