



Canvas Select Plus microSD Memory Card

With Android A1 Performance Class

Kingston's Canvas Select Plus microSD card offers reliable performance, compatible with Android devices and cameras, with speeds up to 150MB/s¹. With A1 app performance, it ensures smooth multitasking and fast load times. Durable and versatile, it's perfect for everyday storage needs.

- Class 10 UHS-I speeds up to 150MB/s¹
- Optimized for use with Android devices
- Capacities up to 1TB²
- Durable³
- Lifetime Warranty

Specifications

| | |
|---------------------------|--|
| Capacities ² | 64GB, 128GB, 256GB, 512GB, 1TB |
| Standard/Class | Class 10, UHS-I, U1/U3, Video Class 10/30, A1 |
| Performance ¹ | 64GB: 100MB/s Read, UHS-I Speed Class, U1, V10, A1 128GB-256GB: 150MB/s Read, UHS-I Speed Class, U1, V10, A1 512GB-1TB: 150MB/s Read, UHS-I Speed Class, U3, V30, A1 |
| microSDXC card dimensions | 11mm x 15mm x 1mm |
| SD adapter dimensions | 24mm x 32mm x 2.1mm |
| Format | exFAT |
| Operating temperature | -25°C~85°C |
| Storage temperature | -40°C~85°C |
| Voltage | 3.3V |
| Warranty/support | Lifetime |

Part Numbers SD Adapter Included

| | | |
|-------------|------------|-------------|
| SDCS3/128GB | SDCS3/1TB | SDCS3/256GB |
| SDCS3/512GB | SDCS3/64GB | |

Part Numbers SD Adapter Not Included

| | | |
|---------------|--------------|---------------|
| SDCS3/128GBSP | SDCS3/1TBSP | SDCS3/256GBSP |
| SDCS3/512GBSP | SDCS3/64GBSP | |

1. Based on internal testing, performance will vary based on host device. Engineered with proprietary technology to reach read speeds beyond UHS-I 104MB/s specification, up to 150MB/s. Write speed may be lower for some capacities. Full performance requires MobileLite Plus Reader.
2. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the products. For more information, go to Kingston's [Flash Memory Guide](#).
3. IEC/EN 60529 IPX7 certified for protection against continual water submersion up to 30 minutes and depth up to 1m. Withstands temperature range from -25°C to 85°C. Protected against X-ray exposure based on ISO7816-1 guidelines.



THIS DOCUMENT SUBJECT TO CHANGE WITHOUT NOTICE.

©2025 Kingston Technology Corporation, 17600 Newhope Street, Fountain Valley, CA 92708 USA. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. MKD-06202025

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kingston:](#)

[SDCS3/256GB](#) [SDCS3/1TB](#) [SDCS3/512GB](#) [SDCS3/128GB](#) [SDCS3/64GB](#)