









| ▲ SWITCH FUNCTION |        |        |
|-------------------|--------|--------|
| POS. 1            | POS. 2 | POS. 3 |
|                   |        |        |
| ON                | OFF    | ON     |
| 2-3               | OPEN   | 2-1    |



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A @ 250 VAC  
5A @ 120 VAC OR 28 VDC
6. ELECTRIC LIFE: 6,000 MAKE-AND-BREAK CYCLES  
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -40°C TO 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. HARDWARE INCLUDED  
T100011 - LOCK WASHER - QTY 1  
T100015 - LOCK RING - QTY 1  
T100000 - HEX NUT - QTY 2

| REV | ECO NO     | DESCRIPTION       | DATE     | BY | E-SWITCH®             |           |     |          | OBJECT ID |
|-----|------------|-------------------|----------|----|-----------------------|-----------|-----|----------|-----------|
| B   | ECO-102793 | 100 SERIES UPDATE | 08/19/24 | MR | TITLE 100DP3T1B3M2QEH |           |     |          | 000023170 |
|     |            |                   |          |    | SCALE                 | DATE      | DR  | DWG      | REV       |
|     |            |                   |          |    | 2:1                   | 7/19/2011 | BGL | ST123014 | B         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[100DP3T1B3M2QEH](#)