





**RECOMMENDED PANEL MOUNTING**

| ▲ SWITCH FUNCTION |        |          |
|-------------------|--------|----------|
| POS. 1            | POS. 2 | POS. 3   |
|                   |        |          |
| ON                | OFF    | (ON)     |
| 2-3, 5-6          | OPEN   | 2-1, 5-4 |

( ) = DENOTES MOMENTARY

**NOTE:**

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 2A @ 250 VAC  
5A @ 120 VAC OR 28 VDC
6. ELECTRIC LIFE: 6,000 MAKE-AND-BREAK CYCLES  
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
9. OPERATING TEMP.: -40°C TO 85°C
10. ▲ DENOTES CRITICAL PARAMETER.

| REV | ECO NO     | DESCRIPTION       | DATE     | BY |                      |                |        |             | OBJECT ID |
|-----|------------|-------------------|----------|----|----------------------|----------------|--------|-------------|-----------|
| C   | ECO-102491 | 100 SERIES UPDATE | 02/21/24 | MR | TITLE 100DP5T1B1M2QE |                |        |             | 000024343 |
|     |            |                   |          |    | SCALE 2:1            | DATE 8/15/2002 | DR CJB | DWG T125000 | REV C     |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[100DP5T1B1M2QE](#)