




RECOMMEND P.C.B. LAYOUT



NO EPOXY ON TERMINALS
BELOW THIS SURFACE ▲



CIRCUIT: SPDT

CONTACT CONFIGURATION

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
<DN>	OFF	<DN>	
2-3	OPEN	2-1	

NOTES: ()=Momentary

- 1. ALL DIMENSIONS IN MM
- 2. TERM. NOS. FOR REF ONLY
- 3. RATING: 0.4 VA Max. @20VAC or DC Max.

2. IERM, NDS, FOR REF ONLY						
3. RATING: 0.4 VA Max, @20VAC or DC Max.						
A	RELEASED FOR PRODUCTION					
REV.	DESCRIPTION	DATE	CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED						
TOLERANCES						
0.0	±0.4					
0.00	±0.25					
<div>E-SWITCH®</div> <div>200 MSP-4 T5 B4 M2 R E</div>						
				TITLE		
				SCALE	DATE	DR
				2:1	11/18/97	MM
			DWG			
			T211043			
			REV			
			A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[200MSP4T5B4M2RE](#)