



200R SERIES TOGGLE SWITCH

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS




APPLICATIONS / MARKETS




Audio / Visual




Consumer Electronics




Vending Machines



Kiosks



Instrumentation



Medical Equipment

RoHS

SPECIFICATIONS

Electrical Rating: 0.4VA Max@ 48V (AC or DC)
Mechanical Life: 40,000 Cycles
Contact Resistance: 50mΩ Max. initial
Insulation Resistance: 1,000MΩ
Dielectric Strength: 500V
Operating/Storage Temperature: -30°C to 85°C
Circuit Function: SP or DP

FEATURES & BENEFITS

- Multiple termination options
- Single or double pole
- Available in both 2 or 3 position circuits
- Miniature in size
- Gold contacts

PART NUMBER CONFIGURATOR

Series	Circuit	Toggle	Bushing	Termination	Contact Material
2 0 0 R	S P 1	T 1	B 1	M 2	R
200R	SP1 - ON-NONE-ON SP2 - ON-NONE-(ON) SP3 - ON-OFF-ON SP4 - (ON)-OFF-(ON) SP5 - ON-OFF-(ON) DP1 - ON-NONE-ON DP2 - ON-NONE-(ON) DP3 - ON-OFF-ON DP4 - (ON)-OFF-(ON) DP5 - ON-OFF-(ON)	T1	B1	M2 M6 M7	R - Gold

* () denotes momentary

Specifications subject to change without notice



E-SWITCH®



www.e-switch.com

800.867.2717



2

M2 TERMINATION

Single Pole





Double Pole





M6 TERMINATION

Single Pole



Double Pole



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[200RDP1T1B1M2R](#) [200RDP1T1B1M6R](#) [200RDP1T1B1M7R](#) [200RDP2T1B1M2R](#) [200RDP2T1B1M6R](#)
[200RDP2T1B1M7R](#) [200RDP3T1B1M2R](#) [200RDP3T1B1M6R](#) [200RDP3T1B1M7R](#) [200RSP1T1B1M2R](#)
[200RSP1T1B1M6R](#) [200RSP1T1B1M7R](#) [200RSP2T1B1M2R](#) [200RSP2T1B1M6R](#) [200RSP2T1B1M7R](#)
[200RSP3T1B1M2R](#) [200RSP3T1B1M6R](#) [200RSP3T1B1M7R](#)