








RECOMMENDED PANEL MOUNTING

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
DN	OFF	DN	
2-3,5-6	OPEN	2-1,5-4	

PANEL THICKNESS
* DIMENSION IS 15.75/15.88
FDR PANEL THICKNESS BETWEEN
1.52mm TO 3.18mm



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC OR 28VDC
2A @250VAC
5. MATERIAL: FIXED TERMINAL & MOVING CONTACT
Copper Alloy w/Silver Plate
6. CONTACT RESISTANCE: 10mILLI Ohms max initial
@2-4VDC, 100ma for AG & AU
7. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
8. INSULATION RESISTANCE: 1,000M ohm min.
9. DIELECTRIC STRENGTH: 1000V RMS @sea level
10. OPERATING TEMP.: -30°C to 85°C
11. 2002/95/EC (ROHS) COMPLIANT

E-SWITCH®

TITLE		SCALE		DATE		DR		DWG		REV	
300DP3R6BLKM3QEBLK		2:1		8/16/07		BF		T3223003		C	
CHANGED DIM. 6.35 TO 6.63		8/16/07		BF		CHKD					
DESCRIPTION		DATE		CHKD							
ECN No.		17567		C							
REV.		17567		C							

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[300DP3R6BLKM3QEBLK](#)