


PANEL THICKNESS

* DIMENSION IS 15.75/15.88
FOR PANEL THICKNESS BETWEEN
1.52mm TD 3.18mm




$\langle \rangle = \text{Momentary}$

2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.4VA @20V AC or DC max.
5. MATERIAL: FIXED TERMINAL & MOVING CONTACT

Copper Alloy w/GOLD plate over Nickel plate.

6. CONTACT RESISTANCE: 10mILLI Ohms max initial @2-4VDC, 100mA for Ag & Au
7. ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.
8. INSULATION RESISTANCE: 1,000M ohm min.
9. DIELECTRIC STRENGTH: 1000V RMS @sea level
10. OPERATING TEMP.: -30°C to 85°C



300 SP-2 R6 BLK M1 R E BLK

REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[300SP2R6BLKM1REBLK](#)