








NOTE:

- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 2A @ 48VDC
5. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
6. INSULATION RESISTANCE: 1,000M Ω @ 500VDC
7. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
8. ELECTRICAL LIFE: 50,000 CYCLES
9. OPERATING TEMPERATURE: -20°C TO 55°C
10. INGRESS PROTECTION: IP65
11. ▲ DENOTES CRITICAL PARAMETER
- ▲ 12. SUPPLIED HARDWARE: O-RING AND HEXNUT
- ▲ 13. ILLUMINATION COLOR: WHITE
- ▲ 14. ILLUMINATION VOLTAGE: BASE VOLTAGE 2.8 V



C	24637	UPDATE THREAD LENGTH TO 15.0	12/10/20	JM
B	23839	UPDATED RATING TO IP66	4/8/19	MJR
A	22715	NEW RELEASE	2/6/17	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE	PV9F2V0SS-301
-------	---------------

SCALE 1:1

DATE 2/6/2017

DR	MJR
----	-----

DWG 52-PV9F2V0SS301

REV
C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PV9F2V0SS-301](#)