


CIRCUIT: SPDT
CONTACT CONFIGURATION

ON	<ON>
2-1	2-3

() = Momentary



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.4VA @ 20V AC or DC max.
- ▲ 5. FIXED TERM. MOVING CONTACT: COPPER ALLOY with
GOLD Plate over Nickel plate
6. ELECTRICAL LIFE: 50,000 make-and-break cycle
at full load.
7. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
8. OPERATING TEMP.: -30°C to 85°C
9. ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH®

B	12575	CHANGE CAP PART NUMBER	12/14/04	AR
A	14257	RELEASED FOR PRODUCTION	8/20/04	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
 IS PROPRIETARY TO E-SWITCH AND IS
 NOT TO BE COPIED OR TRANSFERRED

TITLE

800AWSP8M7REC1BLK

SCALE

2:1

DATE

8/20/04

DR

AR

DWG

XT0127P

REV

B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[800AWSP8M7REC1BLK](#)