


1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: X.X=±0.4
 X.XX=±0.25
 3. TERM. NOS. FOR REFERENCE ONLY.
 4. ELECTRICAL RATING:
 12V DC, 100mA (Resistive Load)
 5. ELECTRICAL LIFE:
 50,000 Cycles
 6. OPERATING FORCE: 50gf max.
 7. TRAVEL: 2.0mm max.
 8. PACKAGING: TAPE AND REEL, 1900 PIECES PER REEL.

OBJECT ID: 000018041

G	15120	REVISED TERMINAL SHAPE	7/28/05	RC	<div style="text-align: center;">  900 AG Q </div>				
F	12884	ADD DIMENSION	3/5/03	CJB					
E	12708	ADD TOP VIEW, REV SCH.	1/9/03	CJB					
D	12139	REVISED AND REDRAWN	5/10/02	CJB					
REV.	ECN No.	DESCRIPTION	DATE	CHKD					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV
					8:1	5/10/02	CJB	P010900	G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[900AGQ](#)