



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 12VDC @ 50mA
4. CONTACT RESISTANCE: 100m Ω MAX.
5. INSULATION RESISTANCE: 100M Ω MIN.
6. OPERATING FORCE: 160 \pm 50gf
7. TRAVEL: 0.2 \pm 0.1mm
8. OPERATING TEMPERATURE: -40°C to 85°C
9. OPERATING LIFE 500,000 CYCLES
10. LED COLOR: RED / GREEN
11. ▲ DENOTED CRITICAL PARAMETER
12. PACKAGE: SWITCHES ARE 450 PIECES PER BAG
BUTTONS WILL BE BAGGED SEPARATELY
13. PART TO BE HALOGEN FREE.
14. BUTTONS TO BE ASSEMBLED ONTO THE BOARD



 E-SWITCH®				
TITLE TL3265RGQTCLR				
SCALE 4:1	DATE 11/2/2018	DR MW	DWG B200082	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL3265RGQTCLR](#)