



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RESISTANCE: 1 OHM MAX.
5. RATING: 1A @ 5-24VDC
6. INGRESS PROTECTION: IP68
7. ELECTRIC LIFE: 50,000,000 CYCLES
8. OPERATING TEMP.: -40°C to 85°C
9. ▲ DENOTES CRITICAL PARAMETER.
10. HARDWARE SUPPLIED: O-RING AND NUT BULK IN BAG



REV	ECO NO	DESCRIPTION	DATE	BY	 <b>E-SWITCH®</b>					OBJECT ID
C	ECO-102092	NOTE 8 -40C TO 85C WAS -20C TO 65C	07/10/23	JS	TITLE CS7M2FR					000023603
B	ECO-101884	PRINT UPDATE	05/18/23	JS						
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 1:1	DATE 9/20/2018	DR rc	DWG T070005	REV C	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[CS7M2FR](#)