






PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040023	D16EET12
2	1	F050201	50-002-04 BLUE OPAQUE RECTANGULAR CONCAVE
3	1	F050420	50-004-20 12VDC LED RED



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
- TERMINAL NUMBERS FOR REF ONLY
- MECHANICAL LIFE: 2,000,000 OPERATIONS
- CONTACT RATING: 5A @ 250 VAC, 8A @ 125 VAC
6A @ 24 VDC
- SEAL RATING: IP40
- MOUNTING PANEL THICKNESS: 0.5 - 5.0 mm
- INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
- OPERATING TEMP.: -25°C to 55°C
- TRAVEL: 3.0mm FULL, 2.0mm LATCH
- LAMP VOLTAGE: 12VDC LED RED
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT.



A	18413	RELEASED FOR PRODUCTION	3/6/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE D16EET12JREDBLU

SCALE 1.5:1

DATE 3/6/2009

DR BLR

DWG XF0788P

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16EET12JREDBLU](#)