





PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040035	D16OAT12
2	1	F052205	50-002-05 WHITE OPAQUE RECTANGULAR CONCAVE LENS



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD min.
- ▲ 5. CONTACT RATING: 5A @ 250VAC UL, VDE
8A @ 125VAC UL, VDE
6A @ 24VDC
6. SEAL RATING: IP40
7. MOUNTING PANEL THICKNESS: 0.5mm - 5.0 mm
8. INSULATION RESISTANCE: 1,000 MILLI-OHM MIN.
9. OPERATING TEMP.: -25°C to 70°C
10. FULL TRAVEL: 3.0 mm
11. LAMP VOLTAGE: NO LAMP
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT.
14. PACKAGE: BOX / 20 PIECES PER BOX



E-SWITCH®



TITLE D16OAT120WHT

A	18613	RELEASED FOR PRODUCTION	8/12/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 1.5:1

DATE 8/12/2009

DR BLR

DWG XF0803P

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAT120WHT](#)