




ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040036	D16OAT13
2	1	F052205	WHITE OPAQUE RECTANGULAR CONCAVE LENS



PANEL MOUNTING






a b (+)

3PDT
CONTACT CONFIGURATION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A @ 250 VAC
6A @ 24 VDC
8A @ 125 VAC
5. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
6. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
7. OPERATING TEMP.: -25°C to 70°C
8. SEAL RATING: IP 40
9. (MOUNTING) PANEL THICKNESS: 0.5 - 5.0 mm
- ▲10. LAMP: NONE
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/05/EC (ROHS) COMPLIANT.
13. PACKAGE: BOX/20 PIECES PER BOX



TITLE D16OAT130WHT

A	18407	RELEASED FOR PRODUCTION	2/26/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:1

DATE 2/26/2009

DR BLR

DWG XF0785P

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAT130WHT](#)