








ISOMETRIC

PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040054	D16OAT23
2	1	F052215	BUTTON ASSY: FLAT TOP, OPAQUE, WHITE, RECTANGLE



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A @250VAC
8A @125VAC
6A @24VDC
5. ELECTRICAL LIFE: >50,000 CYCLES
6. TRAVEL: 3.0MM
7. PANEL THICKNESS: 0.5 - 5 mm
8. SEALED TO IP40.
9. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
10. OPERATING TEMP.: -25 °C to 70 °C
- ▲ 11. LAMP VOLTAGE: NONE
12. ▲ DENOTES CRITICAL PARAMETER.
13. PACKAGE: 20 PIECES PER BOX
14. 2002/95/EC (ROHS) COMPLIANT



A	18196	RELEASED FOR PRODUCTION	8/4/08	BLR	TITLE D16OAT230WHT				
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 1.5:1	DATE 8/4/2008	DR BLR	DWG XF0760P	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[D16OAT230WHT](#)