## **ULV4 SERIES ANTI-VANDAL SWITCH**

DETECTOR SWITCHES

DIP SWITCHES

**KEYLOCK** SWITCHES

NAVIGATION SWITCHES

SPECIFICATIONS

cycles (latching)

Travel: 3.2mm

Electrical Rating: 3A, 125/250VAC

Insulation Resistance: 1000 MQ @ 500VDC

Contact Arrangement: SPDT or DPDT

Mechanical Impact Protection: IK08

Operating/Storage Temperature: -20°C to 55°C

Actuation Force: Single Pole: 2.5N; Double Pole: 3.5N

Electrical Life: 50,000 Cycles

Dielectric Strength: 2,000VAC

Contact Resistance: 50mΩ

Moisture Protection: IP67

Panel Thickness: 1-10mm Hex Nut Torque: 5-14Nm

Agency Approvals: cURus

Mechanical Life: 1,000,000 cycles (momentary); 500,000

PUSHBUTTON SWITCHES

SUIDE SWITCHES

TACTILE SWITCHES

TOGGLE



**Applications** / Markets











211




#### **FEATURES & BENEFITS**

- 19mm diameter panel cutout
- Dot or ring or power illumination options available •
- Multiple switch functions available
- Multiple illumination voltage options
- IP67 rated
- SPDT or DPDT
- **UL** Certified
- · Custom graphics available
- Soldered wire leads (300mm long) optional

### PART NUMBER CONFIGURATOR


E+SWITCH<sup>®</sup>-



## **ULV4 Series Anti-vandal Switch**

Body Dimensions -SPDT

E+SWITCH<sup>®</sup>



## **ULV4 Series Anti-vandal Switch**

M19 x 1.0

THREAD

#### **BODY DIMENSIONS -**DPDT

22.00

[.866 in]


2.00


[.079 in]



**ANTI-VANDAL SWITCHES** 








GRAPHICS OR

ILLUMINATED


POWER SYMBOL



The LED + and - terminals


are not included on the non-illuminated options


**DPDT SWITCH DIMENSIONS** 




6

3







GRAPHICOPTIONS


2 υ

0 Q 0

3 www.e-switch.com 800.867.2717



# ULV4 SERIES ANTI-VANDAL SWITCH



# ULV4 SERIES ANTI-VANDAL

### WIRE LEADS

ANTI-VANDAL SWITCHES

**DETECTOR** SWITCHES

DIP SWITCHES

**KEYLOCK** SWITCHES

TACTILE SWITCHES


**TOGGLE** SWITCHES

CAP OPTIONS

E • SWITCH<sup>®</sup>-

SWITCH	WIRE	LENGTH
SW1-1	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-2	WIRE, 24AWG AWM UL1015, PURPLE	300.0 [11.8 in]
SW1-3	WIRE, 24AWG AWM UL1015, GREEN	300.0 [11.8 in]
SW1-4	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-5	WIRE, 24AWG AWM UL1015, ORANGE	300.0 [11.8 in]
SW1-6	WIRE, 24AWG AWM UL1015, YELLOW	300.0 [11.8 in]
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK	300.0 [11.8 in]
SW1- (+)	WIRE, 24AWG AWM UL1015, RED	300.0 [11.8 in]

\*\* WIRE LEADS PROVIDED ARE DEPENDANT ON THE FUNCTION SELECTED \*\*



5

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

ULV4FWGSS341 ULV4FW3SS331 ULV4FWBSS544 ULV4FWB11544 ULV4FWBSS531