



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: AC 125V 7A, AC 250V 4A
5. CONTACT RESISTANCE: 20m ohm max. at 5V DC 1A.
6. DIELECTRIC STRENGTH: AC 1500V RMS
7. LIFE EXPECTANCY: Electrical: 6,000 cycle
8. OPERATING FORCE: 550±150gf
9. TRAVEL: Full: 5.5mm, Lock: 4.0mm

E-SWITCH®

| TITLE | | | |
|--|---------|-------------------|---------|
| B | 10361 | REVISED & REDRAWN | 9/16/99 |
| REV. | ECN No. | DESCRIPTION | DATE |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED | | | |
| SCALE | | DATE | DR |
| 1.5:1 | | 10/31/95 | MM |
| P227 EE 2B20A | | DWG | P030100 |
| REV | | B | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[P227EE2B20A](#)