



VIEW A-A



CIRCUIT: 3PDT

| SWITCH FUNCTION | | | |
|-----------------|--------|----------------|--|
| PDS. 1 | PDS. 2 | PDS. 3 | |
| | | | |
| DN | DFF | DN | |
| 2-3,5-6 8-9 | OPEN | 2-1,5-4 8-7 | |

CONTACT CONFIGURATION



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲4. RATING: 5 AMPS @ 120VAC OR 28VDC;
2 AMPS @ 250VAC
5. ELECTRIC LIFE: 50,000 make-and-break cycles
at full load.
6. INSULATION RESISTANCE: 1,000 Mega-ohm min.
7. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
8. OPERATING TEMP.: -30°C to 85°C
9. 2002/95/EC (ROHS) COMPLIANT
- ▲10. HARDWARE TO BE SHIPPED BULK
T100011-LOCK WASHER-QTY-1
T100015-LOCK RING-QTY-1
T100000-HEX NUT-QTY-2
11. ▲ DENOTES MAJOR DIMENSION.



| TITLE | | | |
|--|---------|-------------------------|--------|
| 1003P3T1B1M1QEH | | | |
| A | 16974 | RELEASED FOR PRODUCTION | 2/7/07 |
| REV. | ECN No. | DESCRIPTION | DATE |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED | | | |
| SCALE 2:1 | | | |
| DATE 2/7/2007 | | | |
| DR TN DWG ST135009 | | | |
| REV A | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[1003P3T1B1M1QEH](#)