




PANEL THICKNESS	X dimension
0.75-1.25 [0.030-.049]	19.2-.01 [0.756]
1.25-2.0 [0.049-.079]	19.4-.01 [0.764]
2.0-3.0 [0.079-.118]	19.8-.01 [0.780]




PANEL CUTOUT
NOT TO SCALE



SWITCH FUNCTION	
PDS. 1	PDS. 2
ON	OFF
1-1a	OPEN




.80
[0.032] (2 PL)



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 15A @ 125VAC OR
6A @ 250VAC
5. MATERIALS: TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
6. ELECTRIC LIFE: 10,000 cycles
7. CONTACT RESISTANCE: <20 Mega Ω
8. INSULATION RESISTANCE: >1000 Mega Ω
9. DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles



CIRCUIT: SPST

TITLE			R1966A GRY GRY FF		
A	11463	RELEASED FOR PRODUCTION	5/24/01	CJB	
REV.	ECN No.	DESCRIPTION	DATE	CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
SCALE			DATE	DR	DWG
1.5:1			5/24/01	MM	M301236
					REV
					A

E-SWITCH®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R1966AGRYGRYFF](#)