



NOTES:




1. ALL DIMENSION IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
 3. TERM. NOS. FOR REF. ONLY
 4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
 5. OPERATING FORCE: 425 $\pm$ 100 CM/STANDARD
 6. OPERATING TEMP: -30° to 85°C
 7. CIRCUIT 4 Pole: 3 POSITIONS, 30° INDEX.
 8. DIELECTRIC STRENGTH: 1000V RMS min.@SEA LEVEL.
 9. ▲ DESIGNATE MAJOR DIMENSIONS
 10. HARDWARE SUPPLIED ON SWITCH -SEE BELOW
- LOCKING RING, LOCKWASHER, & HEX NUT.



CONTACT CONFIGURATION
Timing: NON-SHORTING



TERMINATION DETAIL
SCALE 2X



E-SWITCH®				
B A REV. 12821 11516 ECN No. REDRAWN RELEASED FOR PRODUCTION DESCRIPTION 2/19/03 2/13/01 DATE CJB RJC CHKD		TITLE KC-43-A-(30.0mm) 01-N-L-S		
SCALE 1.5:1		DATE 2/13/01	DR RJC	DWG G510270
		REV B		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC-43-A-30.0-01-N-L-S](#)