




CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



NOTE:

1. ALL DIMENSIONS IN MM [INCH].
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: SILVER
5. CONTACT RATING: 0.3A @ 125VAC
6. CONTACT RATING: (NON-SWITCHING) 5A
7. OPERATING FORCE 800±300gm-cm
8. OPERATING TEMP: -30°C TO 85°C
- ▲ 9. CIRCUIT SP: 7 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:
(1) LOCKWASHER, (1) HEXNUT, AND (1) STOP RING
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT

ISOMETRIC



B	19363	UPDATED NOTES	10/19/10	BMA
A	18224	RELEASED FOR PRODUCTION	8/28/08	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE KC17A9.501NLS

SCALE 1.5:1

DATE 8/28/2008

DR BLR

DWG G527968

REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[KC17A9.501NLS](#)